



Eaton N234-MI-06N-BX

Medical-Grade Ethernet Network Isolator for
Patient Care Vicinities - RJ45 (F/M), IEC
60601-1, 6 in. Cable, TAA

□□□□

PRODUCT NAME	Eaton Tripp Lite series surge protector
CATALOG NUMBER	N234-MI-06N-BX
UPC	037332287137
PRODUCT LENGTH/DEPTH	0.98 in
PRODUCT HEIGHT	1.84 in
PRODUCT WIDTH	2.63 in
PRODUCT WEIGHT	0.1 lb
WARRANTY	1 year limited
COMPLIANCES	RoHS CE Marked REACH TAA Compliant
CERTIFICATIONS	2MOPP IEC 60601-1

ACCESSORY CLASS	Networking accessories
COLOR	White
CABLE JACKET COLOR	White
PACKAGE CONTENTS	Quick Start Guide N234-MI-06N-BX Medical-Grade Ethernet Network Isolator for Patient Care Vicinities
SYSTEM REQUIREMENTS	Network components that comply with IEEE 802.3 or IEEE 802.3ab (10/100/1000BASE-T, twisted-pair) Cat6 network cabling
IEEE STANDARDS SUPPORTED	802.3
CONNECTOR TYPE	Networking-copper
CABLE JACKET MATERIAL	LSZH
NETWORK SPEED	10 Gbps
PRODUCT HIGHLIGHTS	1-year limited warranty (Worldwide) Compliant with a wide range of medical equipment and Cat6 cables Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases Isolates harmful leakage currents on a data network to protect patients and equipment Meets vigorous IEC 60601-1 2MOPP standards for use in patient care vicinities Plug-and-play operation requires no additional software or external power supply
SIDEA CONNECTOR1	RJ45 (MALE)
SIDEB CONNECTOR1	RJ45 (FEMALE)
ACCESSORY TYPE	Network isolator
SIDEB CONNECTOR3	RJ45 (FEMALE)
TECHNOLOGY	Cat6
OPERATING HUMIDITY	10% to 90% RH, Non-condensing
OPERATING TEMPERATURE RANGE	14° to 158°F (-10° to 70°C)
STORAGE HUMIDITY	10% to 95% RH, Non-

RANGE	condensing
STORAGE TEMPERATURE	-40° to 158°F (-40° to 70°C)
ESD PROTECTION	16kV
OPERATING TEMPERATURE	14° to 158°F (-10° to 70°C)
CONNECTOR GROUP	RJ45
CONNECTOR	RJ45 (female)
