


Eaton N237-P18N-WHSH

Cat6 Junction Box Cable Assembly - Surface Mount, Unshielded, PoE+, RJ45/110 Punchdown, 18-in. (45.72 cm), Blue

PRODUCT NAME	Eaton Tripp Lite series copper coupler
CATALOG NUMBER	N237-P18N-WHSH
UPC	037332250537
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.112 lb
WARRANTY	3 year limited
COMPLIANCES	TAA Compliant

ACCESSORY CLASS	Networking accessories
COLOR	Blue
CABLE JACKET RATING	CMR-LP LP5
CABLE JACKET COLOR	Blue
PACKAGE CONTENTS	(2) Screws N237-P18N-WHSH Cat6 Junction Box Cable Assembly, 18 in., Blue (2) Cable ties
SYSTEM REQUIREMENTS	Cat6 PoE
CONNECTOR TYPE	Networking-copper
PRODUCT FEATURES	TAA Compliant
CABLE JACKET MATERIAL	PVC
NETWORK SPEED	1 Gbps (Gigabit)
PRODUCT HIGHLIGHTS	Cat6 UTP patch cord rated for high-speed 550 MHz/1 Gbps communications Certified IEEE 802.3bt PoE++ cable saves you expense and effort of powering PoE devices individually 3-year limited warranty (Worldwide) Carries CMR-LP5 certification for withstanding temperatures up to 167°F (75°C) Ideal for security cameras, WAPs, LEDs and other ceiling-mount PoE++ devices Supports Type 4 Power over Ethernet (PoE) and PoE++ up to 100 watts
CONTACT PLATING	Gold
SIDEA CONNECTOR1	110 IDC
SIDEB CONNECTOR1	RJ45 (MALE)
ACCESSORY TYPE	Cable assembly kit
SIDEB CONNECTOR3	RJ45 (MALE)
TECHNOLOGY	Cat6 PoE
FEATURES	Flex Center
OPERATING TEMPERATURE RANGE	14° to 140°F (-10° to 60°C)
RELATIVE HUMIDITY	0-90% non-condensing
STORAGE HUMIDITY RANGE	-4° to 158°F (-20° to 70°C)
STORAGE TEMPERATURE	-4° to 158°F (-20° to 70°C)
POWER OVER ETHERNET (POE) POWER - MAX	24 W
CABLE LENGTH	1.5 Foot
NUMBER OF PORTS	0
OUTER CABLE	6.5 +/- 0.3mm



DIAMETER	
OPERATING TEMPERATURE	14° to 140°F (-10° to 60°C)
TAA COMPLIANCE	Yes
CABLE SHEATH MATERIAL	UTP
CONNECTOR GROUP	110 block RJ45
CONNECTOR	RJ45 (male) 110 IDC
POE TYPE	Type 4 High-Power (100W, IEEE 802.3bt)
POWER OVER ETHERNET (POE)	100W (802.3bt)
CABLE STYLE	Regular

:
:
:
: