



Eaton N261-010-AQ

Cat6a 10G Certified Snagless UTP Ethernet Cable (RJ45 M/M), Aqua, 10 ft. (3.05 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series preterminated copper patch cables
CATALOG NUMBER	N261-010-AQ
UPC	037332187680
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.27 lb
COMPLIANCES	REACH IEEE Certified RoHS
CERTIFICATIONS	UL Listed cUL Listed

□□□□		□□	
SPECIAL FEATURES	0% to 90% RH, Non-Condensing		
CABLE JACKET RATING	FT4		
CABLE JACKET COLOR	Aqua		
PACKAGE CONTENTS	10-ft. (3.05 m) Cat6a Black Aqua Cable		
SYSTEM REQUIREMENTS	Cat6a		
IEEE STANDARDS SUPPORTED	802.3at 802.3an		
CONNECTOR TYPE	Networking-copper		
PRODUCT FEATURES	Snagless Connector		
CABLE JACKET MATERIAL	PVC		
NETWORK SPEED	10 Gbps		
PRODUCT HIGHLIGHTS	10-ft. (3.05 m) Augmented Cat6 (CAT6a) Unshielded (UTP) Snagless Patch Cable, Aqua Lifetime limited warranty (Worldwide) 10Gbps Over Copper Each cable Fluke® Tested and Verified		
CONTACT PLATING	Gold		
SIDEA CONNECTOR1	RJ45 (MALE)		
SIDEB CONNECTOR1	RJ45 (MALE)		
SIDEB CONNECTOR3	RJ45 (MALE)		
TECHNOLOGY	Cat6a		
OPERATING HUMIDITY	0% to 90% RH, Non-Condensing		
OPERATING TEMPERATURE RANGE	14° to 104°F (-10° to 40°C)		
STORAGE HUMIDITY RANGE	0% to 90% RH, Non-Condensing		
STORAGE TEMPERATURE	5° to 122°F (-15° to 50°C)		
CONDUCTOR GAUGE	24 AWG		
CABLE LENGTH	10 Foot		
OUTER CABLE DIAMETER	6.2 mm		
NUMBER OF CONDUCTORS	4 Pair		
OPERATING TEMPERATURE	14° to 104°F (-10° to 40°C)		
BANDWIDTH PER TIA STANDARD	500 MHZ		
MAXIMUM BANDWIDTH AS TESTED	600 MHz		
CABLE SHIELDING	UTP		

CABLE LENGTH RANGE	9 - 14ft (2 - 4M)
CABLE SHEATH MATERIAL	UTP
CONNECTOR GROUP	RJ45
CONDUCTOR MATERIAL	Stranded Copper
CONNECTOR	RJ45 (male)
POE TYPE	Type 2 PoE+ (30W, IEEE 802.3at)
WIRING METHOD	EIA/TIA 568B
CABLE STYLE	Molded Snagless
