


Eaton N261-S06-BK

Cat6a 10G Snagless Molded Slim UTP Ethernet Cable (RJ45 M/M), Black, 6 ft. (1.83 m)

PRODUCT NAME	Eaton Tripp Lite series preterminated copper patch cables
CATALOG NUMBER	N261-S06-BK
UPC	037332203908
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.08 lb
WARRANTY	Limited lifetime
COMPLIANCES	RoHS IEEE Certified REACH

SPECIAL FEATURES	0% to 90% RH, Non-Condensing
CABLE JACKET COLOR	Black
PACKAGE CONTENTS	N261-S06-BK Cat6a 10G Snagless Molded Slim UTP Network Patch Cable (M/M), Black, 6-ft. (1.83 m)
SYSTEM REQUIREMENTS	Cat6a
IEEE STANDARDS SUPPORTED	802.3an
CONNECTOR TYPE	Networking-copper
PRODUCT FEATURES	Snagless Connector
CABLE JACKET MATERIAL	PVC
NETWORK SPEED	10 Gbps
PRODUCT HIGHLIGHTS	Easy to route through cable management panels Supports Ethernet speeds up to 10 Gbps Over 38% slimmer than standard Cat6a cables High-quality 28 AWG stranded copper wire Lifetime limited warranty (Worldwide) Snagless RJ45 design protects tabs from damage
CONTACT PLATING	Gold
SIDEA CONNECTOR1	RJ45 (MALE)
SIDEB CONNECTOR1	RJ45 (MALE)
SIDEB CONNECTOR3	RJ45 (MALE)
TECHNOLOGY	Cat6a
OPERATING HUMIDITY	0% to 90% RH, Non-Condensing
OPERATING TEMPERATURE RANGE	14° to 122°F (-10° to 50°C)
STORAGE HUMIDITY RANGE	0% to 90% RH, Non-Condensing
STORAGE TEMPERATURE	5° to 140°F (-15° to 60°C)
CONDUCTOR GAUGE	28 AWG
CABLE LENGTH	6 Foot
OUTER CABLE DIAMETER	3.8 mm
NUMBER OF CONDUCTORS	4 Pair
OPERATING TEMPERATURE	14° to 122°F (-10° to 50°C)
BANDWIDTH PER TIA STANDARD	500 MHz
MAXIMUM BANDWIDTH AS TESTED	600 MHz
CABLE SHIELDING	UTP
CABLE LENGTH RANGE	5 - 8ft (1 - 2M)



CABLE SHEATH MATERIAL	UTP
CONNECTOR GROUP	RJ45
CONDUCTOR MATERIAL	Stranded Copper
CONNECTOR	RJ45 (male)
WIRING METHOD	EIA/TIA 568B
CABLE STYLE	Slim Molded Snagless

:
:
:
: