



Eaton N846-10M-24-P

MTP/MPO Patch Cable with Push/Pull Tab Connectors, 100GBASE-SR10, CXP, 24 Fiber, 100Gb OM3 Plenum-rated - Aqua, 10M (33 ft.)

□□□□

PRODUCT NAME	Eaton Tripp Lite series preterminated fiber patch cable
CATALOG NUMBER	N846-10M-24-P
UPC	037332173829
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.2 lb
WARRANTY	Limited lifetime
COMPLIANCES	RoHS REACH

CABLE JACKET RATING	OFNP
CABLE JACKET COLOR	Aqua
PACKAGE CONTENTS	10 Meter MTP / MPO Patch Cable, 24 Fiber, 100GbE Aqua OM3 Plenum
CONNECTOR COLOR	Aqua Black Blue
CONNECTOR TYPE	Networking-fiber
PRODUCT FEATURES	Push/Pull Tabs
CABLE JACKET MATERIAL	PVC
NETWORK SPEED	100 Gbps 400 Gbps
PRODUCT HIGHLIGHTS	Lifetime limited warranty (Worldwide) OM3 rated 50/125 Multimode Hi-density MTP/MPO 24- fiber connectors for reduced cabling Push/Pull tab connectors offer maximum accessibility in high density installations; install / remove with one hand Supports to 100GbE speeds
SIDEA CONNECTOR1	24F MPO (FEMALE)
SIDEB CONNECTOR1	24F MPO (FEMALE)
TECHNOLOGY	Multimode
OPERATING HUMIDITY	5% to 85% RH, Non- Condensing
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE HUMIDITY RANGE	35% to 65% RH, Non- Condensing
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
BEND RADIUS - MIN	20 mm (Dynamic); 10 mm (Static)
CLAD DIAMETER	125
CORE DIAMETER - MAX	50
INSERTION LOSS	≤ 0.35 dB
NUMBER OF FIBERS	24
FIBER CABLE LENGTH	10M (32.8 ft)
CONNECTOR GROUP	MPO
CONNECTOR	24F MPO (female)
ATTENUATION 850NM	3.0 dB/km

ENDFACE POLISH	PC
OPTICAL MODE	OM3
FIBER TYPE	50/125
