




Eaton P012-006

2-Slot Non-Polarized Laptop Notebook
Power Cord, 1-15P to C7 - 10A, 120V, 18
AWG, 6 ft. (1.83 m), Black

□□□□

PRODUCT NAME	Eaton Tripp Lite series power cord
CATALOG NUMBER	P012-006
UPC	037332013422
PRODUCT LENGTH/DEPTH	0.1 in
PRODUCT HEIGHT	0.1 in
PRODUCT WIDTH	12.3 in
PRODUCT WEIGHT	0.21 lb
WARRANTY	Limited lifetime
COMPLIANCES	RoHS FCC Class B
CERTIFICATIONS	cUL Listed UL Listed CSA certified NOM UL 1778

Specifications	
INPUT CURRENT -MAX	10 Ampere
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
DEVICE COMPATIBILITY	DVR Laptop PDU UPS
AWG-SIZE	18
CABLE LENGTH	6 Foot
NUMBER OF CONDUCTORS	2
OPERATING HUMIDITY	10% to 65% RH
OUTER CABLE DIAMETER	6.9mm
POWER CORD JACKET TYPE	SPT-2
STORAGE HUMIDITY RANGE	10% to 65% RH
WIRE SIZE (AWG) - MAX	0.82
CABLE LENGTH RANGE	5 - 8ft (1 - 2M)
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
PACKAGE CONTENTS	P012-006 2-Slot Non-Polarized Laptop Notebook Power Cord, 1-15P to C7 - 6-ft. (1.83 m), Black
CONNECTOR COLOR	Black
CONNECTOR TYPE	Power
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Straight
PRODUCT HIGHLIGHTS	Ideal replacement for a worn-out or missing laptop power cable Recommended for powering notebook computers and other home/office peripherals 6-ft. (1.83 m) length allows flexibility in placing devices in relationship to AC outlet Lifetime limited warranty (Worldwide)
PLUG COLOR	Black
SIDEA CONNECTOR1	NEMA 1-15P (NON-POLARIZED)
SIDEB CONNECTOR1	IEC-320-C7 (NON-



	POLARIZED)
VOLTAGE RATING	125 VAC
CONNECTOR GROUP	C7 1-15P
CONNECTOR	NEMA 1-15P (non-polarized) IEC 320-C7 (non-polarized)



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

