




Eaton P040-010

Power Cord, C19 to NEMA L6-20 - Heavy-Duty, Locking, 20A, 250V, 12 AWG, 10 ft. (3.05 m), Black

Specifications

PRODUCT NAME	Eaton Tripp Lite series power cord
CATALOG NUMBER	P040-010
UPC	037332140951
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	10.98 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	1.4 lb
WARRANTY	Limited lifetime
COMPLIANCES	RoHS
CERTIFICATIONS	UL Listed cUL Listed

Specifications	
INPUT CURRENT -MAX	20 Ampere
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
RELATIVE HUMIDITY	10% to 65% RH, Non-Condensing
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
DEVICE COMPATIBILITY	Router Server Network Switch PDU UPS
AWG-SIZE	12
CABLE LENGTH	10 Foot
NUMBER OF CONDUCTORS	3
OUTER CABLE DIAMETER	11mm
POWER CORD JACKET TYPE	SJT
STORAGE HUMIDITY RANGE	10% to 65% RH
WIRE SIZE (AWG) - MAX	3.31
CABLE LENGTH RANGE	9 - 14ft (2 - 4M)
COLOR	Black
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
PACKAGE CONTENTS	P040-010 C19 to L6-20P Power Cord, 10-ft. (3.05 m), Black
CONNECTOR COLOR	Black
CONNECTOR TYPE	Power
PRODUCT FEATURES	High Voltage Locking Plug
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Straight
PRODUCT HIGHLIGHTS	Thick 12 AWG wire gauge manages high power levels required for larger equipment C19 to L6-20P power cord is ideal replacement for worn-out or missing cable Recommended for powering servers, switches and other essential network devices L6-20 Locking connector maintains secure link to avoid loss of power and costly downtime



	Lifetime limited warranty (Worldwide) Long 10-ft. (3.05 m) cord provides flexibility in placing connected device away from outlet
PLUG COLOR	White Blue
SIDEA CONNECTOR1	NEMA L6-20P
SIDEB CONNECTOR1	IEC-320-C19
VOLTAGE RATING	250 VAC
CONNECTOR GROUP	C19 L6-20P
CONNECTOR	IEC 320-C19 NEMA L6-20P
