



Eaton P502-001

VGA High-Resolution RGB Coaxial Cable
(HD15 M/M), 1 ft. (0.31 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	P502-001
UPC	037332153210
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.41 lb
COMPLIANCES	RoHS

P502-001	
TYPE	Passive Cable
COLOR	Black
CABLE JACKET COLOR	Black
CONNECTOR TYPE	Video
PACKAGE CONTENTS	P502-001 VGA Coaxial High-Resolution Monitor Cable (M/M), 1 ft.
PRODUCT HIGHLIGHTS	Made from mini-coaxial (RGB) and paired video wire Supports video resolutions up to 2048 x 1536, including 1080p Foil and braid shielding blocks hazardous EMI/RFI line noise Lifetime limited warranty (Worldwide) Gold-plated connectors and contacts for maximum conductivity Integral strain relief protects against cable stress and cracking
SIDEA CONNECTOR1	HD15 (MALE)
SIDEB CONNECTOR1	HD15 (MALE)
SIDEB CONNECTOR3	HD15 (MALE)
TECHNOLOGY	Coax VGA / SVGA VGA/SVGA
CONNECTOR GROUP	VGA
CONNECTOR	HD15 (male)
CABLE LENGTH	1 Foot
OPERATING TEMPERATURE RANGE	14° to 122°F (-10° to 50°C)
STORAGE TEMPERATURE RANGE	5° to 140°F (-15° to 60°C)
CABLE TYPE	Passive
CABLE LENGTH RANGE	Up to 4ft (up to 1M)



