



Eaton P561-010

DVI Single Link Cable, Digital TMDS Monitor Cable (DVI-D M/M), 10 ft. (3.05 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	P561-010
UPC	037332120113
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.59 lb
WARRANTY	Limited lifetime
COMPLIANCES	RoHS

Eaton	
TYPE	Passive Cable
COLOR	Black
CABLE JACKET COLOR	Black
CONNECTOR TYPE	Video
PACKAGE CONTENTS	DVI Single Link TMDS cable - DVI-D, M/M, 10'
PRODUCT HIGHLIGHTS	Resolutions up to 1920 x 1200 Lifetime limited warranty (Worldwide) Compatible with Flat Panel Displays, Digital CRT Displays and Projectors High Speed Digital Transmission to 4.95Gbps Superior molded cables with foil/braid shielding for maximum EMI/RFI protection
SIDEA CONNECTOR1	DVI-D SINGLE LINK (MALE)
SIDEB CONNECTOR1	DVI-D SINGLE LINK (MALE)
SIDEB CONNECTOR3	DVI-D SINGLE LINK (MALE)
TECHNOLOGY	DVI
CONNECTOR GROUP	DVI
CONNECTOR	DVI-D single link (male)
CABLE LENGTH	10 Foot
CABLE TYPE	Passive
CABLE LENGTH RANGE	9 - 14ft (2 - 4M)
