




Eaton P566-010

HDMI to DVI Adapter Cable (M/M), 10 ft. (3.1 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	P566-010
UPC	037332122940
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.3 lb
WARRANTY	Limited lifetime
COMPLIANCES	RoHS

□□□□	
TYPE	Passive Cable
OPERATING HUMIDITY RANGE	10% to 85% RH, Non-Condensing
STORAGE HUMIDITY RANGE	5% to 90% RH, Non-Condensing
COLOR	Black
CABLE JACKET RATING	VW-1
MATERIAL	PVC
CABLE JACKET COLOR	Black
CONNECTOR PLATING	Gold
CONNECTOR TYPE	Video
CABLE JACKET MATERIAL	PVC
PACKAGE CONTENTS	10-ft. (3.05 m) HDMI to DVI Gold Digital Video Cable - HDMI-M/DVI-M
PRODUCT HIGHLIGHTS	Supports a bandwidth up to 5Gbps Supports high-def video resolutions up to 1920 x 1080 @60Hz (1080p). Gold plated connectors and contacts provide optimal signal transfer. Lifetime limited warranty (Worldwide) Premium double shielded digital video cable protects against EMI/RFI noise. This product is covered by a Lifetime Limited Warranty
CONTACT PLATING	Gold
PACKAGING TYPE	Polybag
HDCP SPECIFICATION	1.3
SIDEA CONNECTOR1	HDMI (MALE)
SIDEB CONNECTOR1	DVI-D SINGLE LINK (MALE)
SIDEB CONNECTOR3	DVI-D SINGLE LINK (MALE)
TECHNOLOGY	DVI HDMI
FEATURES	Flex Center
CONNECTOR GROUP	DVI HDMI
CONNECTOR	DVI-D single link (male) HDMI (male)
CABLE LENGTH	10 Foot
CABLE OUTER DIAMETER (OD)	5.5mm
MAX SUPPORTED VIDEO	1920 x 1200 (1080p)



RESOLUTION	
OPERATING TEMPERATURE RANGE	32° to 113°F (0° to 45°C)
STORAGE TEMPERATURE RANGE	14° to 158°F (-10° to 70°C)
CABLE LENGTH RANGE	9 - 14ft (2 - 4M)
