



Eaton P566-016

HDMI to DVI Adapter Cable (M/M), 16 ft. (4.9 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	P566-016
UPC	037332122902
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.69 lb
WARRANTY	Limited lifetime
COMPLIANCES	RoHS

TYPE	Passive Cable
COLOR	Black
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
CONNECTOR TYPE	Video
CABLE JACKET MATERIAL	PVC
PACKAGE CONTENTS	16-ft. (4.88 m) HDMI to DVI Gold Digital Video Cable - HDMI-M/DVI-M
PRODUCT HIGHLIGHTS	Lifetime limited warranty (Worldwide) Premium double shielded digital video cable protects against EMI/RFI noise. Gold plated connectors and contacts provide optimal signal transfer. Supports a bandwidth up to 5Gbps This product is covered by a Lifetime Limited Warranty Supports high-def video resolutions up to 1920 x 1080 @60Hz (1080p).
SIDEA CONNECTOR1	HDMI (MALE)
SIDEB CONNECTOR1	DVI-D SINGLE LINK (MALE)
SIDEB CONNECTOR3	DVI-D SINGLE LINK (MALE)
TECHNOLOGY	HDMI DVI
FEATURES	Flex Center
CONNECTOR GROUP	DVI HDMI
CONNECTOR	HDMI (male) DVI-D single link (male)
CABLE LENGTH	16 Foot
MAX SUPPORTED VIDEO RESOLUTION	1920 x 1200 (1080p)
CABLE TYPE	Passive
MAX RESOLUTION	1080p
CABLE LENGTH RANGE	14 - 20ft (4 - 6M)



