




Eaton P568-003-2A

4K HDMI Cable (M/M) - 4K 60 Hz, 4:4:4, Gripping Connectors, Black, 3 ft.

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	P568-003-2A
UPC	037332236739
PRODUCT LENGTH/DEPTH	0.0001 in
PRODUCT HEIGHT	0.0001 in
PRODUCT WIDTH	0.0001 in
PRODUCT WEIGHT	0.0001 lb
WARRANTY	Limited lifetime
COMPLIANCES	RoHS REACH

□□□□	
TYPE	Passive Cable
AUDIO SPECIFICATION	32-channels; ARC
OPERATING HUMIDITY RANGE	0% to 90% RH, Non-Condensing
RELATIVE HUMIDITY	0-90% non-condensing
STORAGE HUMIDITY RANGE	0% to 90% RH, Non-Condensing
COLOR	Black
CABLE JACKET RATING	VW-1
MATERIAL	PVC
CABLE JACKET COLOR	Black
CONNECTOR COLOR	Gray
CONNECTOR PLATING	Gold
CONNECTOR TYPE	Video
PRODUCT FEATURES	EDID Compatible EDID Support HDR Support Consumer Electronics Control (CEC) Supported Ethernet Support Latching or Gripping Connector 3D Video Supported
CABLE JACKET MATERIAL	PVC
COLOR DEPTH	48-bit Deep color
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	P568-003-2A High-Speed HDMI Cable with Gripping Connectors, M/M, 3 ft.
PRODUCT HIGHLIGHTS	Carries High Dynamic Range (HDR) for richer contrast and expanded color accuracy High-grip HDMI plugs maintain constant A/V signal without accidental disconnections 3 ft. length allows flexibility in placing devices, while avoiding cable clutter Lifetime limited warranty (Worldwide) Supports UHD resolutions up to 4K (4:4:4) for crystal-clear video Plug-and-play operation with no software required for easy, immediate installation



CONTACT PLATING	Gold
CHROMA SUB SAMPLING	4:4:4
HDCP SPECIFICATION	1.4
SIDEA CONNECTOR1	HDMI (MALE)
SIDEB CONNECTOR1	HDMI (MALE)
SIDEB CONNECTOR3	HDMI (MALE)
TECHNOLOGY	HDMI
CONNECTOR GROUP	HDMI
BANDWIDTH	18 Gbps
CONNECTOR	HDMI (male)
SUPPORTED RESOLUTION	1280x720 (720p) 1920x1080 (1080p) 1920 x 1200 2560 x 1600 3840x2160 (4K)
CABLE LENGTH	3 Foot
CABLE OUTER DIAMETER (OD)	6.0 mm
MAX SUPPORTED VIDEO RESOLUTION	3840 x 2160 (4K) @ 60Hz
MINIMUM BEND RADIUS	30mm
LED INDICATORS	0
OPERATING TEMPERATURE RANGE	14° to 122°F (-10° to 50°C)
STORAGE TEMPERATURE RANGE	5° to 140°F (-15° to 60°C)
CABLE TYPE	Passive
SIGNAL TRANSMISSION	Bidirectional
MAX RESOLUTION	4K/60
CABLE LENGTH RANGE	Up to 4ft (up to 1M)

□□□□:
□□□□:
□□□:
□□: