




Eaton P568-010-WH

High-Speed HDMI Cable (M/M) - 4K, Gripping Connectors, White, 10 ft. (3.1 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	P568-010-WH
UPC	037332203533
PRODUCT LENGTH/DEPTH	0.001 in
PRODUCT HEIGHT	0.001 in
PRODUCT WIDTH	0.001 in
PRODUCT WEIGHT	0.001 lb
WARRANTY	Limited lifetime
COMPLIANCES	REACH RoHS

□□□□	
TYPE	Passive Cable
AUDIO SPECIFICATION	Stereo Audio
OPERATING HUMIDITY RANGE	10% to 85% RH, Non-Condensing
STORAGE HUMIDITY RANGE	5% to 90% RH, Non-Condensing
COLOR	White
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	White
CONNECTOR COLOR	White
CONNECTOR PLATING	Gold
CONNECTOR TYPE	Video
PRODUCT FEATURES	EDID Support Consumer Electronics Control (CEC) Supported
CABLE JACKET MATERIAL	PVC
COLOR DEPTH	24-bit True color 24-bit True Color
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	P568-010-WH High-Speed HDMI Cable (M/M), White, 10 ft. (3.1 m)
PRODUCT HIGHLIGHTS	Supports UHD video resolutions up to 4K Backward compatible with previous HDMI generations Gold-plated white connectors for optimal signal transfer Lifetime limited warranty (Worldwide) Premium foil and braid shielding protects against EMI/RFI noise
CONTACT PLATING	Gold
CHROMA SUB SAMPLING	4:4:4
HDCP SPECIFICATION	1.3
SIDEA CONNECTOR1	HDMI (MALE)
SIDEB CONNECTOR1	HDMI (MALE)
SIDEB CONNECTOR3	HDMI (MALE)
TECHNOLOGY	HDMI
FEATURES	Flex Center
CONNECTOR GROUP	HDMI
CONNECTOR	HDMI (male)
CABLE LENGTH	10 Foot



MAX SUPPORTED VIDEO RESOLUTION	3840 x 2160 (4K) @ 30Hz
MINIMUM BEND RADIUS	55mm
LED INDICATORS	0
OPERATING TEMPERATURE RANGE	32° to 113°F (0° to 45°C)
STORAGE TEMPERATURE RANGE	-40° to 176°F (-40° to 80°C)
CABLE TYPE	Passive
SIGNAL TRANSMISSION	Bidirectional
MAX RESOLUTION	4K/30
CABLE LENGTH RANGE	9 - 14ft (2 - 4M)
