




Eaton P569-003-CERT

4K HDMI Cable with Ethernet (M/M) - 4K 60 Hz, Gripping Connectors, 3 ft.

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	P569-003-CERT
UPC	037332198600
PRODUCT LENGTH/DEPTH	6.9 in
PRODUCT HEIGHT	0.5 in
PRODUCT WIDTH	9.2 in
PRODUCT WEIGHT	0.1 lb
WARRANTY	Limited lifetime
COMPLIANCES	REACH RoHS

□□□□	
TYPE	Passive Cable
AUDIO SPECIFICATION	ARC
OPERATING HUMIDITY RANGE	0% to 90% RH, Non-Condensing
STORAGE HUMIDITY RANGE	0% to 90% RH, Non-Condensing
COLOR	Black
CABLE JACKET RATING	VW-1
MATERIAL	PVC
CABLE JACKET COLOR	Black
CONNECTOR COLOR	Burgundy
CONNECTOR PLATING	Gold
CONNECTOR TYPE	Video
PRODUCT FEATURES	EMI/RFI Line Noise Protection Latching or Gripping Connector 3D Video Supported Ethernet Support HDR Support Consumer Electronics Control (CEC) Supported EDID Compatible EDID Support
CABLE JACKET MATERIAL	PVC
COLOR DEPTH	48-bit Deep color
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	P569-003-CERT 4K HDMI Cable with Ethernet (M/M), 3 ft.
PRODUCT HIGHLIGHTS	Ideal for connecting 4K televisions Special high-grip plugs prevent accidental disconnections Tested for highest performance and ultra reliability Lifetime limited warranty (Worldwide) Supports UHD resolutions up to 4K for crystal-clear video
CONTACT PLATING	Gold
CHROMA SUB SAMPLING	4:4:4
HDCP SPECIFICATION	1.4
SIDEA CONNECTOR1	HDMI (MALE)
SIDEB CONNECTOR1	HDMI (MALE)
SIDEB CONNECTOR3	HDMI (MALE)



TECHNOLOGY	HDMI
CONNECTOR GROUP	HDMI
CONNECTOR	HDMI (male)
CABLE LENGTH	3 Foot
MAX SUPPORTED VIDEO RESOLUTION	3840 x 2160 (4K) @ 60Hz
MINIMUM BEND RADIUS	36.5mm
LED INDICATORS	0
OPERATING TEMPERATURE RANGE	14° to 122°F (-10° to 50°C)
STORAGE TEMPERATURE RANGE	5° to 140°F (-15° to 60°C)
CABLE TYPE	Passive
SIGNAL TRANSMISSION	Bidirectional
MAX RESOLUTION	4K/60
CABLE LENGTH RANGE	Up to 4ft (up to 1M)
