




Eaton P569-003

High Speed HDMI Cable with Ethernet, UHD 4K, Digital Video with Audio (M/M), 3 ft. (0.91 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	P569-003
UPC	037332160645
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9.1 in
PRODUCT WIDTH	7.2 in
PRODUCT WEIGHT	0.19 lb
WARRANTY	Limited lifetime
COMPLIANCES	RoHS REACH

□□□□	
TYPE	Passive Cable
AUDIO SPECIFICATION	ARC
OPERATING HUMIDITY RANGE	0% to 90% RH, Non-Condensing
STORAGE HUMIDITY RANGE	0% to 90% RH, Non-Condensing
COLOR	Black
CABLE JACKET RATING	VW-1
MATERIAL	PVC
CABLE JACKET COLOR	Black
CONNECTOR COLOR	Black
CONNECTOR PLATING	Gold
CONNECTOR TYPE	Video
PRODUCT FEATURES	EDID Support 3D Video Supported EDID Compatible Ethernet Support Consumer Electronics Control (CEC) Supported
CABLE JACKET MATERIAL	PVC
COLOR DEPTH	48-bit Deep color
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	3-ft. (0.91 m) High Speed with Ethernet HDMI Cable
PRODUCT HIGHLIGHTS	Video mirroring with iPad2
	Backward compatible to previous HDMI generations
	Supports transmission speeds up to 18 Gbps 3-ft. (0.91 m) High Speed with Ethernet HDMI cable Lifetime limited warranty (Worldwide)
CONTACT PLATING	Gold
CHROMA SUB SAMPLING	4:4:4
HDCP SPECIFICATION	1.4
SIDEA CONNECTOR1	HDMI (MALE)
SIDEB CONNECTOR1	HDMI (MALE)
SIDEB CONNECTOR3	HDMI (MALE)
TECHNOLOGY	HDMI
CONNECTOR GROUP	HDMI
CONNECTOR	HDMI (male)
CABLE LENGTH	3 Foot
CABLE OUTER DIAMETER	6.0 mm



(OD)	
MAX SUPPORTED VIDEO RESOLUTION	3840 x 2160 (4K) @ 30Hz
MINIMUM BEND RADIUS	30mm
LED INDICATORS	0
OPERATING TEMPERATURE RANGE	14° to 122°F (-10° to 50°C)
STORAGE TEMPERATURE RANGE	5° to 140°F (-15° to 60°C)
CABLE TYPE	Passive
SIGNAL TRANSMISSION	Bidirectional
MAX RESOLUTION	4K/30
CABLE LENGTH RANGE	Up to 4ft (up to 1M)



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

