



Eaton SR2POSTDP12HD

SmartRack 45U Heavy-Duty 2-Post Open
Frame Rack, 12-Inch Deep

□□□□

PRODUCT NAME	Eaton Tripp Lite series SmartRack 2-post open frame rack
CATALOG NUMBER	SR2POSTDP12HD
UPC	037332266569
PRODUCT LENGTH/DEPTH	13.5 in
PRODUCT HEIGHT	85.83 in
PRODUCT WIDTH	20.3 in
PRODUCT WEIGHT	91.73 lb
WARRANTY	5 year limited
COMPLIANCES	EIA-310-E RoHS
CERTIFICATIONS	IEC 60297-3



Powering Business Worldwide

□□□□	
FEATURES	Flex Center
COLOR	Black
LOAD CAPACITY (STATIC)	2000 lb
MATERIAL	Steel
MOUNTING RAILS	12-24 threaded vertical mounting rails
NUMBER OF RACK UNITS	45U
PACKAGE CONTENTS	• (2) Side channels • (2) Base plates • (2) External waterfall brackets • (14) Cable hooks • (2) Accessory brackets for wire basket attachment • Internal waterfall brace • Assembly hardware • Equipment mounting hardware • Owner's manual
PRODUCT FEATURES	Extra Wide Built-in Cable Management Assembly Required Mounting Holes or Slots
RACK DEPTH	Deep
PRODUCT HIGHLIGHTS	Made of heavy-duty steel with 12-24 threaded and numbered mounting holes 5-year limited warranty (Worldwide) 45U 2-post open frame rack is 12 inches deep to provide more equipment mounting points Cable waterfalls, hooks and accessory bracket enhance cable management Maximum load capacity is 2000 lb. Accommodates toolless button mounting for PDUs and cable managers
RACK HEIGHT	45U
MAXIMUM DEVICE DEPTH	48 Inch
NUMBER OF VERTICAL	2

MOUNTING RAILS	
WEIGHT CAPACITY STATIONARY	2000 Pound
MODULE RACK TYPE	Open-frame
