



Eaton SR2POSTDP24HD

SmartRack 45U Heavy-Duty 2-Post Open
Frame Rack, 24-Inch Deep

□□□□

PRODUCT NAME	Eaton Tripp Lite series SmartRack 2-post open frame rack
CATALOG NUMBER	SR2POSTDP24HD
UPC	037332266576
PRODUCT LENGTH/DEPTH	26 in
PRODUCT HEIGHT	85.83 in
PRODUCT WIDTH	20.3 in
PRODUCT WEIGHT	91.8 lb
WARRANTY	5 year limited
COMPLIANCES	EIA-310-E RoHS
CERTIFICATIONS	IEC 60297-3



Powering Business Worldwide

FEATURES	Flex Center
COLOR	Black
LOAD CAPACITY (STATIC)	2000 lb
MATERIAL	Steel
MOUNTING RAILS	12-24 threaded vertical mounting rails
NUMBER OF RACK UNITS	45U
PACKAGE CONTENTS	• (2) Side channels • (2) Base plates • (2) External waterfall brackets • (14) Cable hooks • (2) Accessory brackets for wire basket attachment • Internal waterfall brace • Assembly hardware • Equipment mounting hardware • Owner's manual
PRODUCT FEATURES	Extra Wide Built-in Cable Management Assembly Required Mounting Holes or Slots
RACK DEPTH	Deep
PRODUCT HIGHLIGHTS	5-year limited warranty (Worldwide) Cable waterfalls, hooks and accessory bracket enhance cable management Made of heavy-duty steel with 12-24 threaded and numbered mounting holes Maximum load capacity is 2000 lb. Accommodates toolless button mounting for PDUs and cable managers 45U 2-post open frame rack is 24 inches deep to provide more equipment mounting points
RACK HEIGHT	45U
MAXIMUM DEVICE DEPTH	48 Inch
NUMBER OF VERTICAL	2

MOUNTING RAILS	
WEIGHT CAPACITY STATIONARY	2000 Pound
MODULE RACK TYPE	Open-frame
