




Eaton SR48UB

48U SmartRack Standard-Depth Rack
Enclosure Cabinet with doors & side panels

□□□□

PRODUCT NAME	Eaton Tripp Lite series SmartRack rack enclosure
CATALOG NUMBER	SR48UB
UPC	037332138446
PRODUCT LENGTH/DEPTH	43 in
PRODUCT HEIGHT	89 in
PRODUCT WIDTH	23.63 in
PRODUCT WEIGHT	315 lb
WARRANTY	5 year limited
COMPLIANCES	RoHS CE Marked
CERTIFICATIONS	UL 60950-1

□□□□	
FEATURES	Flex Center
COLOR	Black
LOAD CAPACITY (DYNAMIC)	2250 lb
LOAD CAPACITY (STATIC)	3500 lb
NUMBER OF RACK UNITS	48U
PACKAGE CONTENTS	• SR48UB Smart Rack Enclosure • (4) Side panels • (4) Side panel locks • (2) Door & side panel keys • (50) M6 screws • (50) M6 cage nuts • (50) M6 washers • Owner's Manual
SURFACE FINISH	Powder Coating
PRODUCT FEATURES	Built-in Cable Management Pre-Installed Casters
RACK DEPTH	Standard
PRODUCT HIGHLIGHTS	Massive front to rear ventilation capacity Meets all enclosure requirements towards PCI DSS (Payment Card Industry Data Security Standard) Compliance Preinstalled casters and leveling feet Ships fully assembled Standard 24" width for optimizing floor space 3500 lbs (1588 kgs) stationary / 2250 lbs (1020.6 kgs) rolling load capacity 4 interior vertical posts with unthreaded square hole openings Locking, removable, reversible front and rear doors 5-year limited warranty (Worldwide) Locking, removable side panels keyed alike with doors 48U SmartRack enclosure with doors and side panels Includes 50 pieces of M6 cage nuts and 50 pieces of



	M6 screws (equipment mounting hardware)
RACK HEIGHT	48U
MAXIMUM DEVICE DEPTH	37 Inch
NUMBER OF VERTICAL MOUNTING RAILS	4
FACTORY PRESET RACK DEPTH	27.75 in
MINIMUM DEVICE DEPTH	4 in
WEIGHT CAPACITY ROLLING	2250 lb
GROUNDING DETAILS	Front and Back door frames
WEIGHT CAPACITY STATIONARY	3500 Pound
MODULE RACK TYPE	Enclosure



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

