



Eaton SRX42UBEXP

42U Server Rack, Euro-Series - Expandable Cabinet, Standard Depth, Side Panels Not Included

□□□□

PRODUCT NAME	Eaton Tripp Lite series SmartRack rack enclosure
CATALOG NUMBER	SRX42UBEXP
UPC	037332221599
PRODUCT LENGTH/DEPTH	41.25 in
PRODUCT HEIGHT	78.5 in
PRODUCT WIDTH	23.622 in
PRODUCT WEIGHT	225 lb
WARRANTY	5 year limited
COMPLIANCES	RoHS CE Marked
CERTIFICATIONS	UL 60950-1

□□□□	
FEATURES	Flex Center
COLOR	Black
LOAD CAPACITY (DYNAMIC)	2250 lb
LOAD CAPACITY (STATIC)	3500 lb
MATERIAL	Steel
NUMBER OF RACK UNITS	42U
PACKAGE CONTENTS	• (2) Keys • (50) M6 screws • (50) M6 washers • (50) M6 cage nuts • Owner's manual
PRODUCT FEATURES	Pre-Installed Casters
RACK DEPTH	Mid
PRODUCT HIGHLIGHTS	5-year limited warranty (Worldwide) Comes without side panels for easy baying with multiple rack cabinets in a row Front and split rear doors lock securely to help prevent damage, tampering or theft 42U rack constructed from powder-coated steel that stands up to tough environments Ships fully assembled for quick deployment on pre-installed casters Mounting rails accept standard rack equipment up to 850 mm deep
RACK HEIGHT	42U
APPLICATION	Store and organize rack-mount equipment in a network closet, data center or other area where you need components to be secure
NUMBER OF VERTICAL MOUNTING RAILS	4
FACTORY PRESET RACK DEPTH	27.75 in
MINIMUM DEVICE DEPTH	4 in
WEIGHT CAPACITY ROLLING	2250 lb
GROUNDING DETAILS	Front and Back door frames

□□

MODULE RACK TYPE	Enclosure
------------------	-----------



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

