



Eaton SRXFANROOF

SmartRack Roof-Mounted Fan Panel - 6
208/240V high-performance fans; 420 CFM;
C14 inlet

□□□□

PRODUCT NAME	Eaton Tripp Lite series SmartRack cooling fan
CATALOG NUMBER	SRXFANROOF
UPC	037332144553
PRODUCT LENGTH/DEPTH	37 in
PRODUCT HEIGHT	3 in
PRODUCT WIDTH	23.5 in
PRODUCT WEIGHT	22 lb
WARRANTY	2 year limited
COMPLIANCES	EIA-310-E RoHS

SmartRack		SmartRack	
INPUT CONNECTION	IEC C14 inlet dongle (user-supplied input cord required)		
NOMINAL INPUT VOLTAGE DESCRIPTION	208-240V AC 50/60 Hz		
CABLE LENGTH	0.5 in		
INPUT FREQUENCY	50/60 Hz		
CABLE LENGTH RANGE	Up to 4ft (up to 1M)		
ACCESSORY CLASS	Cooling accessories		
ACCESSORY TYPE	Airflow management		
COOLING TYPE	Passive		
PACKAGE CONTENTS	6 inch C14 inlet dongle (user-supplied input cord required) Tooless mounting hardware SRXFANROOF 208-240V 50/60Hz fan roof		
INPUT NOMINAL VOLTAGE	208 VAC 230 VAC 240 VAC 208-240V AC 50/60 Hz		
PRODUCT FEATURES	IEC C14 inlet dongle (user-supplied input cord required)		
PRODUCT HIGHLIGHTS	Cold rolled steel with black finish 2-year limited warranty (Worldwide) Ideal for increasing the ventilation of SmartRacks Tooless mounting hardware included Features (6) 208-240V fans mounted in a roof panel Roof Mount Fan Panel - 208-240V		
VOLTAGE RATING	208 VAC 230 VAC 240		

