



Eaton U022-006

USB 2.0 A to B Cable (M/M), 6 ft. (1.83 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	U022-006
UPC	037332100016
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.16 lb
WARRANTY	Limited lifetime
COMPLIANCES	RoHS CE Marked REACH FCC Compliant

□□□□	
OPERATING HUMIDITY RANGE	0% to 90% RH, Non-Condensing
STORAGE HUMIDITY RANGE	0% to 90% RH, Non-Condensing
CABLE JACKET COLOR	Black
CONNECTOR TYPE	USB/Thunderbolt/Lightning
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	6-ft. USB 2.0 Gold Cable USB-A to USB-B
PRODUCT HIGHLIGHTS	Lifetime limited warranty (Worldwide) Premium double-shielded cables with tinned copper braid and aluminum mylar foil feature twisted 28AWG data lines, and 24AWG power lines. Meets or Exceeds USB 2.0 Specifications Gold plated connectors provide superior conductivity Supports faster data transfer rate (1.5 to 480 Mbps) for low speed and high speed devices, including multimedia applications
SIDEA CONNECTOR1	USB A (MALE)
SIDEB CONNECTOR1	USB B (MALE)
OPERATING TEMPERATURE	14° to 122°F (-10° to 50°C)
OPERATING TEMPERATURE RANGE	14° to 122°F (-10° to 50°C)
STORAGE TEMPERATURE RANGE	5° to 140°F (-15° to 60°C)
SIDEB CONNECTOR3	USB B (MALE)
TECHNOLOGY	USB 2.0 (High Speed)
CABLE LENGTH	5 - 8ft (1 - 2M)
CABLE TYPE	Passive
CONNECTOR GROUP	USB-A USB-B
WIRE GAUGE (AWG)	28/24
CABLE LENGTH RANGE	5 - 8ft (1 - 2M)
CONNECTOR	USB B (male) USB A (male)

□□
