



Eaton U038-003-GY-MAX

Heavy-Duty USB-A to USB-C Cable, USB 2.0, UHMWPE and Aramid Fibers, (M/M), Gray, 3 ft. (0.91 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	U038-003-GY-MAX
UPC	037332241320
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.06 lb
WARRANTY	Limited lifetime
COMPLIANCES	CE Marked RoHS REACH

APPLICATION

- Charge and sync your MacBook, Chromebook or other USB-C device from a USB computer or wall charger up to 3 ft. away
- Transfer data between an external hard drive and your USB-C notebook or computer
- Replace a cable that became frayed or inoperable due to frequent use
- Carry in your laptop bag, backpack or briefcase as a durable spare cable

AMPERAGE RATING	3A
OPERATING HUMIDITY RANGE	0% to 90% RH, Non-Condensing
RELATIVE HUMIDITY	0-90% non-condensing
STORAGE HUMIDITY RANGE	0% to 90% RH, Non-Condensing
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
CONNECTOR PLATING	Nickel
CONNECTOR TYPE	USB/Thunderbolt/Lightning
USB SPECIFICATION	USB 2.0 (up to 480 Mbps)
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	U038-003-GY-MAX Heavy-Duty USB-A to USB-C Cable (M/M), Gray, 3 ft. (0.9 m)
PRODUCT HIGHLIGHTS	Integral strain relief helps cable move freely without stress or cracking Lifetime limited warranty (Worldwide) Engineered using UHMWPE and Aramid fiber to stand up to frequent and rigorous use Extra-strong cable construction helps prevent fraying and loose cable connectors

	Reversible USB-C plug connects in either direction for immediate no-fuss use Supports USB 2.0 speeds up to 480 Mbps to ensure efficient charging and data transfers
CONTACT PLATING	Gold
SIDEA CONNECTOR1	USB A (MALE)
SIDEB CONNECTOR1	USB C (MALE)
OPERATING TEMPERATURE	-4° to 140°F (-20° to 60°C)
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE TEMPERATURE RANGE	-4° to 176°F (-20° to 80°C)
SIDEB CONNECTOR3	USB C (MALE)
TECHNOLOGY	USB 2.0 (High Speed)
DATA TRANSFER RATE	480 Mbps
CABLE LENGTH	Up to 4ft (up to 1M)
CABLE OUTER DIAMETER (OD)	3.4 mm
CABLE TYPE	Passive
CONNECTOR GROUP	USB-A USB-C
MATERIAL	PVC, UHMWPE, Aramid
POWER PROVIDED TO CONNECTED DEVICE(S)	15W (5V/3A)
TOTAL CHARGING WATTS	15 W
CABLE LENGTH RANGE	Up to 4ft (up to 1M)
CONNECTOR	USB A (male) USB C (male)

□□□□:
□□□□:
□□□:
□□: