



Eaton U040-003-C

USB-C Cable (M/M) - USB 2.0, Black, 3 ft.
(0.91 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	U040-003-C
UPC	037332263629
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.05 lb
WARRANTY	Limited lifetime
COMPLIANCES	RoHS REACH

Specifications		Features	
AMPERAGE RATING	3A		
OPERATING HUMIDITY RANGE	10% to 85%, Non-Condensing		
STORAGE HUMIDITY RANGE	10% to 85%, Non-Condensing		
CABLE JACKET RATING	VW-1		
USB POWER DELIVERY (PD) CHARGING SUPPORT	Yes		
CABLE JACKET COLOR	Black		
CONNECTOR PLATING	Nickel		
CONNECTOR TYPE	USB/Thunderbolt/Lightning		
PRODUCT FEATURES	USB Charging		
USB SPECIFICATION	USB 2.0 (up to 480 Mbps)		
CABLE JACKET MATERIAL	PVC		
CONNECTOR STYLE	Straight		
PACKAGE CONTENTS	U040-003-C USB-C to USB-C Cable, M/M, Black, 3 ft. (0.9 m)		
PRODUCT HIGHLIGHTS	Compatible with all USB-C and Thunderbolt 3 devices, including Nintendo Switch 2 Reversible USB-C plugs connect in either direction for immediate no-fuss use Power Delivery cable supports 20V 3A (60W) power output for charging host device Supports USB 2.0 speeds up to 480 Mbps to ensure efficient data transfers Lifetime limited warranty (Worldwide)		
CONTACT PLATING	Gold		
SIDEA CONNECTOR1	USB C (MALE)		
SIDEB CONNECTOR1	USB C (MALE)		
OPERATING TEMPERATURE	14° to 140°F (-10° to 60°C)		
OPERATING TEMPERATURE RANGE	14° to 140°F (-10° to 60°C)		
STORAGE TEMPERATURE RANGE	-4° to 158°F (-20° to 70°C)		
SIDEB CONNECTOR3	USB C (MALE)		
TECHNOLOGY	USB 2.0 (High Speed)		
CABLE LENGTH	Up to 4ft (up to 1M)		

MAXIMUM INPUT WATTS	60 W
CABLE OUTER DIAMETER (OD)	3.0MM
CABLE TYPE	Passive
CONNECTOR GROUP	USB-C
MATERIAL	PVC
POWER PROVIDED TO CONNECTED DEVICE(S)	60W (20V/3A)
CABLE LENGTH RANGE	Up to 4ft (up to 1M)
CONNECTOR	USB C (male)



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

