



Eaton U050-010-GY-MAX

Heavy-Duty USB 2.0 USB-A to Micro-B Cable
- M/M, UHMWPE and Aramid Fibers, Gray,
10 ft. (3.05 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	U050-010-GY-MAX
UPC	037332238962
PRODUCT LENGTH/DEPTH	10 in
PRODUCT HEIGHT	0.5 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.22 lb
WARRANTY	Limited lifetime
COMPLIANCES	RoHS REACH CE Marked FCC Compliant



Powering Business Worldwide

APPLICATION	- Charge and sync your smartphone or other Micro-B device from a USB computer or wall charger up to 10 ft. away - Transfer data between an external hard drive or flash drive and your laptop or computer - Replace a cable that became frayed or inoperable due to frequent use
AMPERAGE RATING	2A
OPERATING HUMIDITY RANGE	0% to 90% RH, Non-Condensing
RELATIVE HUMIDITY	0-90% non-condensing
STORAGE HUMIDITY RANGE	0% to 90% RH, Non-Condensing
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
CONNECTOR PLATING	Nickel
CONNECTOR TYPE	USB/Thunderbolt/Lightning
USB SPECIFICATION	USB 2.0 (up to 480 Mbps)
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	U050-010-GY-MAX Heavy-Duty USB-A to USB Micro-B Cable (M/M), Gray, 10 ft. (3 m)
PRODUCT HIGHLIGHTS	Extra-strong cable construction helps prevent fraying and loose cable connectors Ideal for streaming video and other applications that require a fast, clear signal Integral strain relief helps cable move freely without stress or cracking Lifetime limited warranty (Worldwide) Engineered using UHMWPE and Aramid fiber to stand up to frequent and rigorous use Supports USB 2.0 speeds

	up to 480 Mbps to ensure efficient charging and data transfers
CONTACT PLATING	Gold
SIDEA CONNECTOR1	USB A (MALE)
SIDEB CONNECTOR1	MICRO-USB B (MALE)
OPERATING TEMPERATURE	-4° to 140°F (-20° to 60°C)
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE TEMPERATURE RANGE	-4° to 176°F (-20° to 80°C)
SIDEB CONNECTOR3	MICRO-USB B (MALE)
TECHNOLOGY	USB 2.0 (High Speed)
DATA TRANSFER RATE	480 Mbps
CABLE LENGTH	9 - 14ft (2 - 4M)
CABLE OUTER DIAMETER (OD)	4.2mm
CABLE TYPE	Passive
CONNECTOR GROUP	Micro USB USB-A
MATERIAL	PVC, UHMWPE, Aramid
POWER PROVIDED TO CONNECTED DEVICE(S)	10W (5V/2A)
TOTAL CHARGING WATTS	10 W
CABLE LENGTH RANGE	9 - 14ft (2 - 4M)
CONNECTOR	Micro USB-B (male) USB A (male)

□□□□:
□□□□:
□□□:
□□: