




Eaton U223-007

7-Port USB 2.0 Hub

□□□□

PRODUCT NAME	Eaton Tripp Lite series hub
CATALOG NUMBER	U223-007
UPC	037332185389
PRODUCT LENGTH/DEPTH	1.3 in
PRODUCT HEIGHT	0.6 in
PRODUCT WIDTH	6.5 in
PRODUCT WEIGHT	0.14 lb
COMPLIANCES	RoHS FCC Compliant CE Marked REACH

□□□□	
TYPE	Hub
ACCESSORIES	No
AC POWER ADAPTER PLUG(S)	NEMA 1-15P North America
RELATIVE HUMIDITY	10% to 90 % RH, Non-Condensing
COLOR	Black
MATERIAL	ABS
USB HUB PORTS	Yes
CONNECTOR PLATING	Nickel
USB SPECIFICATION	USB 2.0 (up to 480 Mbps)
PACKAGE CONTENTS	External power supply (Input: 100-240V, 50/60 Hz, 0.4A; Output: 5V 2A) with 4 ft. (1.2 m) cord and NEMA 1-15P plug U223-007 7-Port USB 2.0 Hub USB Mini-B to USB-A cable (M/M)
PRODUCT HIGHLIGHTS	3-year limited warranty (Worldwide) Bus-powered hub includes optional external power supply for extra power Compatible with all major operating systems, including Windows and macOS Plug-and-play operation with no software required for easy, immediate installation Supports USB 2.0 speeds up to 480 Mbps to ensure reliable data transfers Blue LED indicates the hub is receiving power from the included supply
PACKAGING TYPE	Box
PLUG COLOR	White Blue
EXTERNAL POWER SUPPLY CERTIFICATIONS	DOE FCC UL
POWER SOURCE TYPE	AC Adapter
SIDEA CONNECTOR1	USB MINI-B 5-PIN (FEMALE)
SIDEB CONNECTOR1	USB A (FEMALE)
DATA PORTS	USB A (FEMALE) USB-A - USB 2.0



DC BARREL PLUG	OD: 3.5 x 1.35 x 8 mm, positive pin, negative sleeve
SIDEB CONNECTOR3	USB A (FEMALE)
VOLTAGE COMPATIBILITY (VAC)	100 VAC 110 VAC 120 VAC 127 VAC 200 VAC 208 VAC 220 VAC 230 VAC 240
HOST CONNECTOR	USB A (MALE)
TECHNOLOGY	USB 2.0 (High Speed)
FEATURES	Flex Center
AC POWER ADAPTER CORD LENGTH	4 ft
NUMBER OF PORTS	7
NUMBER OF USB HUB PORTS	7
POWER CONSUMPTION	0 W
NUMBER OF MONITORS SUPPORTED	0
STORAGE TEMPERATURE RANGE	14° to 194°F (-10° to 90°C)
BTUS	1 BTU/Hr
MOUNTING DETAILS	No
DATA PORTS DETAILS	USB-A - USB 2.0

□□□□:
□□□□:
□□□:
□□: