



Eaton U280-005-ST

5-Port USB Charging Station with Built-In Device Storage, 12V 4A (48W) USB Charger Output

□□□□

PRODUCT NAME	Eaton Tripp Lite series multi-device charger
CATALOG NUMBER	U280-005-ST
UPC	037332199584
PRODUCT LENGTH/DEPTH	4.882 in
PRODUCT HEIGHT	0.787 in
PRODUCT WIDTH	6.614 in
PRODUCT WEIGHT	1.3 lb
WARRANTY	2 year limited
COMPLIANCES	RoHS REACH FCC Compliant

Specifications	
TYPE	Charging Station
AC ADAPTER	Input: 100-240V, 50/60Hz, 1.5A; Output: 12V, 4A
AC POWER ADAPTER CORD LENGTH	5 ft
AC POWER ADAPTER INPUT SPECS (V / HZ / A)	100-240V / 50/60Hz / 1.5A
AC POWER ADAPTER OUTPUT SPECS (V / A)	12V / 4A
CHARGING PORTS DETAILS	USB-A: 12V/4A
NUMBER OF CHARGING PORTS	5
TOTAL CHARGING AMPS	4A
TOTAL CHARGING WATTS	48
POWER CONSUMPTION DETAIL	12.7W (Operating) 0.23W (Standby)
POWER CONSUMPTION	12.7 W
NUMBER OF PORTS	5
OVERLOAD PROTECTION	Yes
CHARGING METHOD DETAIL	5V - 1.5A (7W)
LED INDICATORS	Blue (Power)
OPERATING TEMPERATURE RANGE	41° to 95°F (5° to 35°C)
STORAGE TEMPERATURE RANGE	-4° to 122°F (-20° to 50°C)
AC POWER ADAPTER PLUG(S)	NEMA 1-15P North America
RELATIVE HUMIDITY	20% to 80% RH, Non-Condensing
COLOR	Black
INPUT PLUG TYPE	NEMA 1-15P (NON-POLARIZED)
MATERIAL	Polycarbonate
CHARGING PORTS / AMPS	2.4A
CHARGING METHOD	USB
CONNECTOR TYPE	USB/Thunderbolt/Lightning
	Power
INPUT NOMINAL VOLTAGE	120 VAC 230 VAC
PRODUCT FEATURES	Overvoltage Protection Overcurrent Protection

PACKAGE CONTENTS	Quick Start Guide (7) Storage brackets C7 to NEMA 1-15P power cord, 5 ft. External power supply (Input: 100–240V, 50/60 Hz, 1.5A; Output: 12V, 4A) U280-005-ST 5-Port USB Charging Station
PRODUCT HIGHLIGHTS	5V, 2.4A per port for charging battery-intensive devices Protects against overheating, overcurrent and overcharging 7 adjustable storage brackets for organizing devices All five ports support USB Battery Charging (BC) specification v1.2 External dual-voltage power supply with NEMA 1-15P plug Storage compartment neatly organizes your cabling 2-year limited warranty (Worldwide)
CHARGING FORM FACTOR	Charging hub
CHARGING PORT TYPE	USB A (FEMALE)
PACKAGING TYPE	Box
EXTERNAL POWER SUPPLY CERTIFICATIONS	CCC cUL FCC TUV UL GS PSE RoHS
POWER SOURCE TYPE	AC Adapter
SIDEA CONNECTOR1	NEMA 1-15P (NON-POLARIZED)
SIDEB CONNECTOR1	USB A (FEMALE)
DC BARREL PLUG	OD: 5.5 x 2.5 x 10 mm, positive pin, negative sleeve
SIDEB CONNECTOR3	USB A (FEMALE)
DEVICE COMPATIBILITY	Amazon Kindle Phone Tablet
VOLTAGE COMPATIBILITY (VAC)	100 VAC 110 VAC 120 VAC

