



Eaton U280-007-CQC-ST

7-Port USB Charging Station with Quick Charge 3.0, USB-C Port, Device Storage, 5V 4A (60W) USB Charge Output

□□□□

PRODUCT NAME	Eaton Tripp Lite series multi-device charger
CATALOG NUMBER	U280-007-CQC-ST
UPC	037332199577
PRODUCT LENGTH/DEPTH	4.882 in
PRODUCT HEIGHT	0.866 in
PRODUCT WIDTH	6.614 in
PRODUCT WEIGHT	1.4 lb
WARRANTY	2 year limited
COMPLIANCES	REACH FCC Compliant RoHS

□□□□

□□

TYPE	Charging Station
AC ADAPTER	Input: 100-240V, 50/60Hz, 1.5A; Output: 15V, 4A
AC POWER ADAPTER CORD LENGTH	3 ft
AC POWER ADAPTER INPUT SPECS (V / HZ / A)	100-240V / 50/60Hz / 1.5A
AC POWER ADAPTER OUTPUT SPECS (V / A)	15V / 4A
CHARGING PORTS DETAILS	USB-A: 5V/2.4A USB-A QC: 3.6V~6.5V/3A, 6.5V~9V/2A, 9V~12V/1.5A USB-C: 5V/3A
NUMBER OF CHARGING PORTS	7
TOTAL CHARGING AMPS	9.1A
TOTAL CHARGING WATTS	60
POWER CONSUMPTION DETAIL	15.6W (Operating) 0.07W (Standby)
POWER CONSUMPTION	15.6 W
NUMBER OF PORTS	7
OVER CURRENT PROTECTION	Yes
OVERLOAD PROTECTION	Yes
CHARGING METHOD DETAIL	Quick Charge 3.0; 5V - 1.5A (7W)
INPUT CURRENT	1.5A
INPUT FREQUENCY	50 / 60 Hz
LED INDICATORS	Blue (Power)
OPERATING TEMPERATURE RANGE	41° to 95°F (5° to 35°C)
QUICK CHARGE COMPLIANT	3
STORAGE TEMPERATURE RANGE	-4° to 122°F (-20° to 50°C)
AC POWER ADAPTER PLUG(S)	NEMA 1-15P North America
RELATIVE HUMIDITY	20% to 80% RH, Non-Condensing
COLOR	Black
INPUT PLUG TYPE	NEMA 1-15P (NON-POLARIZED)
MATERIAL	Polycarbonate
USB POWER DELIVERY (PD) CHARGING SUPPORT	Yes

CHARGING PORTS / AMPS	2.4A 3A 3A / 2A / 1.5A
CHARGING METHOD	USB
CONNECTOR TYPE	Power USB/Thunderbolt/Lightning
INPUT NOMINAL VOLTAGE	230 VAC 120 VAC
PRODUCT FEATURES	Battery Charging (5V/1.5A Port) Overvoltage Protection Overcharge Protection USB Charging Overcurrent Protection
PACKAGE CONTENTS	U280-007-CQC-ST 7-Port USB Charging Station C7 to NEMA 1-15P power cord, 5 ft. External power supply (Input: 100–240V, 50/60 Hz, 1.5A; Output: 15V, 4A) (9) Storage brackets Quick Start Guide
PRODUCT HIGHLIGHTS	5 USB-A ports provide up to 5V, 2.4A of charging power and are USB Battery Charging (BC) specification v1.2 compliant Quick Charge 3.0 port charges up to 4x faster than normal charging 2-year limited warranty (Worldwide) USB-C port provides up to 5V, 3A of charging power 9 adjustable storage brackets for organizing devices Storage compartment neatly organizes your cabling
CHARGING FORM FACTOR	Charging hub
CHARGING PORT TYPE	USB C (FEMALE) USB A (FEMALE)
PACKAGING TYPE	Box
EXTERNAL POWER SUPPLY CERTIFICATIONS	FCC TUV GS CCC UL PSE RoHS cUL
POWER SOURCE TYPE	AC Adapter

SIDEA CONNECTOR1	NEMA 1-15P (NON-POLARIZED)
SIDEB CONNECTOR1	USB A (FEMALE)
SIDEB CONNECTOR2	USB C (FEMALE)
DC BARREL PLUG	OD: 5.5 x 2.5 x 10 mm, positive pin, negative sleeve
SIDEB CONNECTOR3	USB A (FEMALE)
DEVICE COMPATIBILITY	Tablet Phone Amazon Kindle
VOLTAGE COMPATIBILITY (VAC)	100 VAC 110 VAC 120 VAC 125 VAC 127 VAC 200 VAC 208 VAC 220 VAC 230 VAC 240
CONNECTOR GROUP	1-15P USB-A
CONNECTOR	NEMA 1-15P (non-polarized) USB A (female)
USB POWER DELIVERY (PD) CHARGING SPECIFICATION	2

□□□□:
□□□□:
□□□:
□□: