



Eaton U322-010-BK

USB 3.2 Gen 1 SuperSpeed Device Cable (A to B M/M) Black, 10 ft. (3.05 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	U322-010-BK
UPC	037332183132
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.27 lb
WARRANTY	Limited lifetime
COMPLIANCES	CE Marked FCC Compliant REACH RoHS ENERGY STAR certified FCC Class B
CERTIFICATIONS	RETIE CSA certified NOM UL 1778

□□□□	
RELATIVE HUMIDITY	10% to 85%, Non-Condensing
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
CONNECTOR PLATING	Nickel
CONNECTOR TYPE	USB/Thunderbolt/Lightning
USB SPECIFICATION	USB 3.2 Gen 1 (up to 5 Gbps)
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	10-ft. USB 3.2 Gen 1 SuperSpeed A-B Device Cable - Black
PRODUCT HIGHLIGHTS	Lifetime limited warranty (Worldwide) 10-ft SuperSpeed USB 3.2 Gen 1 A-B Cable 10 times faster than USB 2.0 with transfer rates up to 5 Gbps
CONTACT PLATING	Gold
SIDEA CONNECTOR1	USB A (MALE)
SIDEB CONNECTOR1	USB B (MALE)
OPERATING TEMPERATURE	14° to 140°F (-10° to 60°C)
OPERATING TEMPERATURE RANGE	14° to 140°F (-10° to 60°C)
STORAGE TEMPERATURE RANGE	-4° to 185°F (-20° to 85°C)
SIDEB CONNECTOR3	USB B (MALE)
TECHNOLOGY	USB 3.x
CABLE LENGTH	9 - 14ft (2 - 4M)
CABLE OUTER DIAMETER (OD)	5.5MM
CABLE TYPE	Passive
CONNECTOR GROUP	USB-B USB-A
MATERIAL	PVC
CABLE LENGTH RANGE	9 - 14ft (2 - 4M)
CONNECTOR	USB A (male) USB B (male)

□□
