



Eaton U325-006

USB 3.0 SuperSpeed A to A Cable for Tripp Lite USB 3.0 All-in-One Keystone/Panel Mount Couplers (M/M), Black, 6 ft. (1.83 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	U325-006
UPC	037332205100
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.39 lb
WARRANTY	Limited lifetime
COMPLIANCES	REACH RoHS

□□□□		□□	
OPERATING HUMIDITY RANGE	0% to 90% RH, Non-Condensing		
STORAGE HUMIDITY RANGE	0% to 90% RH, Non-Condensing		
CABLE JACKET RATING	VW-1		
CABLE JACKET COLOR	Black		
CONNECTOR PLATING	Nickel		
CONNECTOR TYPE	USB/Thunderbolt/Lightning		
USB SPECIFICATION	USB 3.0 (up to 5 Gbps) USB 3.1 Gen 1 (up to 5 Gbps) USB 3.2 Gen 1 (up to 5 Gbps)		
CONNECTOR STYLE	Straight		
PACKAGE CONTENTS	U325-006 USB 3.2 Gen 1 SuperSpeed A/A Cable (M/M), Black, 6 ft.		
PRODUCT HIGHLIGHTS	Backward compatible with legacy USB 2.0 and USB 1.1 peripherals Foil/braid shielding protects against EMI/RFI line noise that can distort or destroy data Plug-and-play operation with no drivers required for easy, immediate installation Supports USB 3.2 Gen 1 speeds up to 5 Gbps to ensure fast data transfers Lifetime limited warranty (Worldwide) Integral strain relief helps cable move freely without stress or cracking		
CONTACT PLATING	Gold		
SIDEA CONNECTOR1	USB A (MALE)		
SIDEB CONNECTOR1	USB A (MALE)		
OPERATING TEMPERATURE	14° to 122°F (-10° to 50°C)		
OPERATING TEMPERATURE RANGE	14° to 122°F (-10° to 50°C)		
STORAGE TEMPERATURE RANGE	5° to 140°F (-15° to 60°C)		
SIDEB CONNECTOR3	USB A (MALE)		
HOST CONNECTOR	USB A (MALE)		
TECHNOLOGY	USB 3.x		
CABLE LENGTH	5 - 8ft (1 - 2M)		

CABLE OUTER DIAMETER (OD)	5.5mm
CABLE TYPE	Passive
CONNECTOR GROUP	USB-A
MATERIAL	PVC
CABLE LENGTH RANGE	5 - 8ft (1 - 2M)
CONNECTOR	USB A (male)
