



Eaton U326-006

USB 3.0 SuperSpeed Device Cable (A to Micro-B M/M), Blue, 6 ft. (1.83 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	U326-006
UPC	037332158147
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.06 lb
WARRANTY	Limited lifetime
COMPLIANCES	FCC Compliant REACH RoHS CE Marked

□□□□		□□	
RELATIVE HUMIDITY	10% to 85%, Non-Condensing		
CABLE JACKET RATING	VW-1		
CABLE JACKET COLOR	Blue		
CONNECTOR PLATING	Nickel		
CONNECTOR TYPE	USB/Thunderbolt/Lightning		
USB SPECIFICATION	USB 3.0 (up to 5 Gbps)		
CONNECTOR STYLE	Straight		
PACKAGE CONTENTS	6-ft. (1.83 m) USB 3.0 SuperSpeed A-Male to Micro-B Male		
PRODUCT HIGHLIGHTS	6-ft. (1.83 m) SuperSpeed USB 3.0 A to Micro-B Cable 10 times faster than USB 2.0, with transfer rates up to 5 Gbps Lifetime limited warranty (Worldwide)		
CONTACT PLATING	Gold		
SIDEA CONNECTOR1	USB 3.0 A (MALE)		
SIDEB CONNECTOR1	USB 3.0 MICRO-B (MALE)		
OPERATING TEMPERATURE	14° to 140°F (-10° to 60°C)		
OPERATING TEMPERATURE RANGE	14° to 140°F (-10° to 60°C)		
STORAGE TEMPERATURE RANGE	-4° to 185°F (-20° to 85°C)		
SIDEB CONNECTOR3	USB 3.0 MICRO-B (MALE)		
TECHNOLOGY	USB 3.x		
CABLE LENGTH	5 - 8ft (1 - 2M)		
CABLE OUTER DIAMETER (OD)	5.5MM		
CABLE TYPE	Passive		
CONNECTOR GROUP	USB-A Micro USB		
MATERIAL	PVC		
CABLE LENGTH RANGE	5 - 8ft (1 - 2M)		
CONNECTOR	USB 3.0 Micro-B (male) USB 3.0 A (male)		

