



Eaton U329-000-10G

USB-C Female to USB-A Male Adapter, USB 3.0, 10G.

□□□□

PRODUCT NAME	Eaton Tripp Lite series USB adapter
CATALOG NUMBER	U329-000-10G
UPC	037332282064
PRODUCT LENGTH/DEPTH	1.1 in
PRODUCT HEIGHT	0.31 in
PRODUCT WIDTH	0.63 in
PRODUCT WEIGHT	0.02 lb
WARRANTY	3 year limited
COMPLIANCES	FCC Compliant RoHS CE Marked REACH
CERTIFICATIONS	UL Listed EN 55024 EN 55032

DEVICE COMPATIBILITY	Phone
	Amazon Kindle
	Laptop
	Chromebook
	Computer
	Tablet
OPERATING HUMIDITY RANGE	10% to 85% RH, Non-Condensing
STORAGE HUMIDITY RANGE	5% to 90% RH, Non-Condensing
COLOR	Black
CONNECTOR PLATING	Nickel
CONNECTOR TYPE	USB/Thunderbolt/Lightning
PRODUCT FEATURES	Bus Powered USB Charging
USB SPECIFICATION	USB 3.2 Gen 2 (Up to 10 Gbps)
PACKAGE CONTENTS	U329-000-10G USB-C to USB-A Adapter (F/M)
PRODUCT HIGHLIGHTS	3-year limited warranty (Worldwide)
	Backwards compatible with previous USB generations
	Plug and play with no external power or software required
	Supports USB 3.2 Gen 2 data transfer speeds up to 10 Gbps for connecting hard drives and other data intensive tasks
	Produces 900mA (0.9A) for charging and powering phones and other mobile devices
	Converts a male USB-C connector to a male USB-A connector
CONTACT PLATING	Gold
SIDEA CONNECTOR1	USB A (MALE)
COMPATIBLE DEVICES	Chromebook
	Laptop
	Smartphone
	Tablet
SIDEB CONNECTOR1	USB C (FEMALE)
OPERATING TEMPERATURE	32° to 113°F (0° to 45°C)
OPERATING TEMPERATURE RANGE	32° to 113°F (0° to 45°C)
STORAGE TEMPERATURE RANGE	14° to 158°F (-10° to 70°C)

DATA PORTS	USB-C - USB 3.2 Gen 2 (10 Gbps) USB C (FEMALE)
SIDEB CONNECTOR3	USB C (FEMALE)
TECHNOLOGY	USB USB 3.x
DATA TRANSFER RATE	10 Gbps
CABLE LENGTH	Up to 4ft (up to 1M)
NUMBER OF PORTS	1
TOTAL NUMBER OF PORTS	1
DATA PORTS DETAILS	USB-C - USB 3.2 Gen 2 (10 Gbps)
CONNECTOR GROUP	USB-C USB-A
MATERIAL	PVC, UL94V-0
POWER PROVIDED TO CONNECTED DEVICE(S)	900MA Downstream Power for Connected USB-C Devices
CONNECTOR	USB A (male)
