



Eaton U360-007-IND

7-Port Industrial-Grade USB 3.0 SuperSpeed Hub - 20 kV ESD Immunity, Metal Housing, Mountable

□□□□

PRODUCT NAME	Eaton Tripp Lite series hub
CATALOG NUMBER	U360-007-IND
UPC	037332186300
PRODUCT LENGTH/DEPTH	2.5 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	5.5 in
PRODUCT WEIGHT	0.7 lb
WARRANTY	3 year limited
COMPLIANCES	CE Marked FCC Compliant RoHS REACH

APPLICATION

- Connect up to 7 USB devices and peripherals to your computer or laptop
- Add easy-to-access USB ports to computers stored in a cabinet, behind furniture or other hard-to-reach location
- Mount to a wall or DIN rail in a harsh environment, such as a factory, construction site, supply room or warehouse

TYPE	Hub
ACCESSORIES	Yes
RELATIVE HUMIDITY	5% to 90% RH, Non-Condensing
COLOR	Black
MATERIAL	Steel (Galvanized Cold Rolled)
USB HUB PORTS	Yes
PRODUCT FEATURES	Bus Powered Industrial Grade
USB SPECIFICATION	USB 3.0 (up to 5 Gbps) USB 3.1 Gen 1 (up to 5 Gbps) USB 3.2 Gen 1 (up to 5 Gbps)
PACKAGE CONTENTS	U360-007-IND 7-Port Industrial-Grade USB 3.0 SuperSpeed Hub Owner's manual USB 3.0 cable, 3 ft. DIN rail-mounting hardware Wall-mounting hardware 3-pin power terminal block
PRODUCT HIGHLIGHTS	ESD protection to ±20 kV cuts potential static damage to your connected peripherals Supports USB 3.0 SuperSpeed rates up to 5 Gbps to ensure fast data transfers Rugged metal housing designed to withstand

	harsh warehouse and factory environments Adds barcode scanner, serial device, sensor—up to 7 devices—to your host computer Plug-and-play operation with no software required for easy, immediate installation 3-year limited warranty (Worldwide)
PACKAGING TYPE	Box
PLUG COLOR	Blue White
POWER SOURCE TYPE	USB
SIDEA CONNECTOR1	USB 3.0 A (MALE)
SIDEB CONNECTOR1	USB 3.0 A (FEMALE)
DATA PORTS	USB-A - USB 3.2 Gen 1 (5 Gbps) USB A (FEMALE)
DC BARREL PLUG	OD: 5.5 x 2.1 x 9.5 mm, positive pin, negative sleeve
SIDEB CONNECTOR3	USB 3.0 A (FEMALE)
VOLTAGE COMPATIBILITY (VAC)	100 VAC 110 VAC 120 VAC 125 VAC 127 VAC 200 VAC 208 VAC 220 VAC 230 VAC 240
HOST CONNECTOR	USB A (MALE)
TECHNOLOGY	USB 3.x
FEATURES	Flex Center
AC ADAPTER	Input: 100-240V, 50/60Hz, 0.6A; Output: 9-40V, 3A
NUMBER OF PORTS	7
NUMBER OF USB HUB PORTS	7
POWER CONSUMPTION	32 W
NUMBER OF MONITORS SUPPORTED	0
STORAGE TEMPERATURE RANGE	14° to 176°F (-10° to 80°C)
BTUS	110.6 BTU/Hr
OVER CURRENT PROTECTION	Yes

