



Eaton U360-007

7-Port USB 3.0 SuperSpeed Hub with BC 1.2 Charging, USB-A

□□□□

PRODUCT NAME	Eaton Tripp Lite series hub
CATALOG NUMBER	U360-007
UPC	037332178480
PRODUCT LENGTH/DEPTH	3.54 in
PRODUCT HEIGHT	5.51 in
PRODUCT WIDTH	5.91 in
PRODUCT WEIGHT	0.25 lb
WARRANTY	3 year limited
COMPLIANCES	FCC Compliant RoHS WEEE Directive EAC



Powering Business Worldwide

APPLICATION

- Connect up to 7 USB peripherals, such as an external hard drive, MP3 player, power meter and printer, to your MacBook, Chromebook or Surface
- Add easy-to-access USB ports to computers stored in a cabinet, behind furniture or other hard-to-reach location

TYPE	Hub
AC POWER ADAPTER PLUG(S)	NEMA 1-15P North America
RELATIVE HUMIDITY	20% to 80% RH, Non-Condensing
COLOR	Black
MATERIAL	ABS
USB HUB PORTS	Yes
CHARGING PORTS / AMPS	2A
CONNECTOR PLATING	Nickel
PRODUCT FEATURES	USB Charging
USB SPECIFICATION	USB 3.0 (up to 5 Gbps) USB 3.1 Gen 1 (up to 5 Gbps) USB 3.2 Gen 1 (up to 5 Gbps)
PACKAGE CONTENTS	U360-007 7-Port USB 3.0 SuperSpeed Hub External power supply with 5 ft. cord and NEMA 1-15P plug (Input: 100–240V, 50/60 Hz, 1.5A Max; Output: 12V 3A) USB 3.0 cable, 3 ft.
PRODUCT HIGHLIGHTS	7 USB-A ports support BC 1.2 specifications for charging mobile devices at 5V 2.4A Adds webcam, flash drive, scanner—up to 7 devices—to your host computer 3-year limited warranty (Worldwide)

	Plug-and-play operation with no software required for easy, immediate installation Compact unit works with USB-enabled operating systems, including Windows and Mac USB 3.0 ports support SuperSpeed rates up to 5 Gbps to ensure fast data transfers
PACKAGING TYPE	Box
PLUG COLOR	Blue White
EXTERNAL POWER SUPPLY CERTIFICATIONS	cUL RoHS
POWER SOURCE TYPE	AC Adapter
SIDEA CONNECTOR1	USB 3.0 A (MALE)
SIDEB CONNECTOR1	USB 3.0 A (FEMALE)
DATA PORTS	USB A (FEMALE) USB-A - USB 3.2 Gen 1 (5 Gbps)
DC BARREL PLUG	OD: 5.5 x 2.5 x 10 mm, positive pin, negative sleeve
SIDEB CONNECTOR3	USB 3.0 A (FEMALE)
VOLTAGE COMPATIBILITY (VAC)	100 VAC 110 VAC 120 VAC 125 VAC 127 VAC 200 VAC 208 VAC 220 VAC 230 VAC 240
HOST CONNECTOR	USB A (MALE)
CHARGING AMPS PER PORT	2 A
TECHNOLOGY	USB 3.x
FEATURES	Flex Center
CHARGING PORTS	USB-A: 5V 1.5A (7.5W) 2.4A Quick Charge
AC ADAPTER	Input: 100-240V, 50/60Hz, 0.8A Max / Output: 12V, 2A
AC POWER ADAPTER CORD LENGTH	5 ft
NUMBER OF PORTS	7
NUMBER OF USB HUB PORTS	7

POWER CONSUMPTION	1 W
NUMBER OF MONITORS SUPPORTED	0
STORAGE TEMPERATURE RANGE	-4° to 185°F (-20° to 85°C)
BTUS	4.8 BTU/Hr
OVER CURRENT PROTECTION	2.93A
DATA PORTS DETAILS	USB-A - USB 3.2 Gen 1 (5 Gbps)
