



Eaton U360-412

6-Port USB 3.0 SuperSpeed Charging Hub -
2x USB 3.0, 4x USB 2.0, 1 charging port

□□□□

PRODUCT NAME	Eaton Tripp Lite series hub
CATALOG NUMBER	U360-412
UPC	037332173560
PRODUCT LENGTH/DEPTH	2.4 in
PRODUCT HEIGHT	0.9 in
PRODUCT WIDTH	4 in
PRODUCT WEIGHT	0.15 lb
WARRANTY	3 year limited
COMPLIANCES	RoHS REACH FCC Compliant CE Marked
CERTIFICATIONS	cUL Listed UL Listed

□□□□	
TYPE	Hub
CHARGING PORTS DETAILS	Dedicated charging port
AC POWER ADAPTER PLUG(S)	NEMA 1-15P North America
COLOR	Black
MATERIAL	ABS
USB HUB PORTS	Yes
CONNECTOR PLATING	Nickel
PRODUCT FEATURES	USB Charging
PACKAGE CONTENTS	USB 7-port Hub USB 3.0 A-B cable, 3ft External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.9A; Output: 5V, 4A)
PRODUCT HIGHLIGHTS	One dedicated port for Tablet charging (5V, 2A) USB 3.0 Hub with two USB 3.0 SuperSpeed ports and four USB 2.0 High-Speed ports USB 2.0 ports support up to 500mA per port Plug-and-Play - no software or drivers required 3-year limited warranty (Worldwide) USB 3.0 ports support up to 900mA per port
PACKAGING TYPE	Box
PLUG COLOR	Blue White
EXTERNAL POWER SUPPLY CERTIFICATIONS	UL FCC cUL RoHS
POWER SOURCE TYPE	AC Adapter
SIDEA CONNECTOR1	USB 3.0 A (MALE)
SIDEB CONNECTOR1	USB 3.0 A (FEMALE)
SIDEB CONNECTOR2	USB A (FEMALE)
DATA PORTS	USB-A - USB 3.2 Gen 1 (5 Gbps) USB-A - USB 2.0 USB A (FEMALE)
HOST CONNECTOR	USB A (MALE)
CHARGING AMPS PER PORT	2 A



TECHNOLOGY	USB 3.x
FEATURES	Flex Center
CHARGING PORTS	USB-A: 2A
AC ADAPTER	Input: 100-240V, 50/60Hz, 0.9A; Output: 5V, 4A
AC POWER ADAPTER CORD LENGTH	5 ft
NUMBER OF USB HUB PORTS	6
POWER CONSUMPTION	2 W
NUMBER OF MONITORS SUPPORTED	0
STORAGE TEMPERATURE RANGE	-4° to 185°F (-20° to 85°C)
BTUS	5.5 BTU/Hr
DATA PORTS DETAILS	USB-A - USB 3.2 Gen 1 (5 Gbps) USB-A - USB 2.0



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

