



Eaton U420-003-G2

USB-C Cable (M/M) - USB 3.2 Gen 2 (10 Gbps), Thunderbolt 3 Compatible, 3 ft. (0.91 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	U420-003-G2
UPC	037332197368
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	6.5 in
PRODUCT WEIGHT	0.001 lb
WARRANTY	3 year limited
COMPLIANCES	REACH RoHS FCC Compliant CE Marked

□□□□	
DEVICE COMPATIBILITY	Headphones
	Laptop
	Chromebook
	Amazon Kindle
	Tablet
	Phone
	Video Game System
RELATIVE HUMIDITY	Watch
	10% to 85% RH, Non-Condensing
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
CONNECTOR PLATING	Nickel
CONNECTOR TYPE	USB/Thunderbolt/Lightning
PRODUCT FEATURES	DisplayPort Alt Mode
USB SPECIFICATION	USB 3.2 Gen 2 (Up to 10 Gbps)
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	U420-003-G2 USB 3.2 Gen 2 Cable, USB-C (M/M), 3 ft.
PRODUCT HIGHLIGHTS	USB 3.2 Gen 2 data transfer speeds up to 10 Gbps
	Error-free signal quality and EMI/RFI protection
	Power output up to 3A for fast-charging devices
	3-year limited warranty (Worldwide)
	Compatible with both USB-C and Thunderbolt 3 ports
	Reversible USB-C male connectors on both ends
CONTACT PLATING	Gold
SIDEA CONNECTOR1	USB C (MALE)
COMPATIBLE DEVICES	Portable Speaker
	Smartphone
	Tablet
	Video Game Console
SIDEB CONNECTOR1	USB C (MALE)
OPERATING TEMPERATURE	14° to 140°F (-10° to 60°C)
OPERATING TEMPERATURE RANGE	14° to 140°F (-10° to 60°C)
STORAGE TEMPERATURE RANGE	-4° to 185°F (-20° to 85°C)
SIDEB CONNECTOR3	USB C (MALE)
TECHNOLOGY	
	USB 3.x

	Thunderbolt
CABLE LENGTH	Up to 4ft (up to 1M)
NUMBER OF MONITORS SUPPORTED	1
CABLE OUTER DIAMETER (OD)	5.2MM
CABLE TYPE	Passive
CONNECTOR GROUP	USB-C
MATERIAL	PVC
MAX SUPPORTED VIDEO RESOLUTION	4096 x 2160 (4K)
RESOLUTIONS SUPPORTED	Capable of transmitting Ultra High Definition (UHD) video up to 4K x 2K (3840 x 2160) @ 30 Hz from hosts that support USB-C DP Alt Mode
CABLE LENGTH RANGE	Up to 4ft (up to 1M)
CONNECTOR	USB C (male)
SUPPORTED RESOLUTION	3840x2160 (4K)

□□□□:
□□□□:
□□□:
□□: