



Eaton U420-01M-RA

USB-C Cable (M/M) - USB 3.2 Gen 1 (5 Gbps),
Thunderbolt 3 Compatible, Right-Angle Plug,
1 m (3.3 ft.)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	U420-01M-RA
UPC	037332263643
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.06 lb
WARRANTY	3 year limited
COMPLIANCES	FCC Compliant RoHS CE Marked REACH

APPLICATION	• Charge and power your MacBook Pro, Windows laptop or other USB-C or Thunderbolt 3 device from a USB-C wall charger • Transfer data between an external hard drive and your laptop or PC • Connect your laptop to a docking station or hub with a USB-C or Thunderbolt 3 port
AMPERAGE RATING	3A
OPERATING HUMIDITY RANGE	10% to 85% RH, Non-Condensing
STORAGE HUMIDITY RANGE	10% to 85% RH, Non-Condensing
CABLE JACKET RATING	VW-1
USB POWER DELIVERY (PD) CHARGING SUPPORT	Yes
CABLE JACKET COLOR	Black
CONNECTOR PLATING	Nickel
CONNECTOR TYPE	USB/Thunderbolt/Lightning
PRODUCT FEATURES	3D Video Supported HDR Support DisplayPort Alt Mode
USB SPECIFICATION	USB 3.0 (up to 5 Gbps) USB 3.1 Gen 1 (up to 5 Gbps) USB 3.2 Gen 1 (up to 5 Gbps)
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Angled
PACKAGE CONTENTS	U420-01M-RA USB-C to USB-C Cable, M/M, Black, 1 m (3.3 ft.)
PRODUCT HIGHLIGHTS	Space-saving right-angle USB-C plug allows easy connection in confined spaces Power Delivery cable supports 20V 3A (60W) power output for charging host device Supports USB 3.2 Gen 1

	speeds up to 5 Gbps to ensure fast data transfers 3-year limited warranty (Worldwide) Supports DisplayPort Alt Mode for transmitting 4K video to a connected display USB-C to USB-C cable is compatible with all USB-C and Thunderbolt 3 devices
--	---

CONTACT PLATING	Gold
SIDEA CONNECTOR1	USB C (MALE) - RIGHT ANGLE
SIDEB CONNECTOR1	USB C (MALE)
OPERATING TEMPERATURE	14° to 140°F (-10° to 60°C)
OPERATING TEMPERATURE RANGE	14° to 140°F (-10° to 60°C)
STORAGE TEMPERATURE RANGE	-4° to 158°F (-20° to 70°C)
SIDEB CONNECTOR3	USB C (MALE)

TECHNOLOGY	Thunderbolt USB 3.x
CABLE LENGTH	Up to 4ft (up to 1M)
MAXIMUM INPUT WATTS	60 W
CABLE OUTER DIAMETER (OD)	4.5MM
CABLE TYPE	Passive
CONNECTOR GROUP	USB-C
MATERIAL	PVC
POWER PROVIDED TO CONNECTED DEVICE(S)	60W (20V/3A)
CABLE LENGTH RANGE	Up to 4ft (up to 1M)
CONNECTOR	USB C (male) USB C right angle (male)
SUPPORTED RESOLUTION	3840 x 4320 (4K) 7680 x 2160 (8K)

