



Eaton U422-20N-G2

USB-C to USB-B Cable (M/M) - USB 3.2, Gen 2 (10 Gbps), Thunderbolt 3 Compatible, 20-in. (50.8 cm)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	U422-20N-G2
UPC	037332243416
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.05 lb
WARRANTY	Limited lifetime
COMPLIANCES	RoHS REACH

- APPLICATION
- Connect a printer or scanner to the USB-C or Thunderbolt 3 port on your computer or laptop
 - Charge and sync a USB-C or Thunderbolt 3 mobile device from a USB-B wall charger up to 20 in. away
 - Connect your laptop to a docking station or hub with a USB-B port

RELATIVE HUMIDITY	10 to 85% RH, Non-Condensing
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
CONNECTOR PLATING	Nickel
CONNECTOR TYPE	USB/Thunderbolt/Lightning
USB SPECIFICATION	USB 3.2 Gen 2 (Up to 10 Gbps)
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	U422-20N-G2 USB-C 3.2 Gen 2 to USB Type-B Cable (M/M), 20 in. (51 cm)
PRODUCT HIGHLIGHTS	Reversible USB-C plug connects in either direction for immediate no-fuss use Plug-and-play operation with no software required for easy, immediate installation Supports USB 3.2 Gen 2 speeds up to 10 Gbps to ensure lightning-fast data transfers USB-C to USB Type-B cable compatible with USB-B, USB-C and Thunderbolt 3 devices Lifetime limited warranty (Worldwide)
CONTACT PLATING	Gold
SIDEA CONNECTOR1	USB C (MALE)
SIDEB CONNECTOR1	USB B (MALE)
OPERATING TEMPERATURE	14° to 140°F (-10° to 60°C)
OPERATING	14° to 140°F (-10° to 60°C)

TEMPERATURE RANGE	
STORAGE TEMPERATURE RANGE	-4° to 185°F (-20° to 85°C)
SIDE B CONNECTOR	USB B (MALE)
TECHNOLOGY	USB 3.x Thunderbolt
CABLE LENGTH	Up to 4ft (up to 1M)
CABLE OUTER DIAMETER (OD)	4.5MM
CABLE TYPE	Passive
CONNECTOR GROUP	USB-B USB-C
MATERIAL	PVC
CABLE LENGTH RANGE	Up to 4ft (up to 1M)
CONNECTOR	USB C (male) USB B (male)
