



Eaton U428-C03-G2

USB-C to USB-A Cable (M/M), USB 3.2 Gen 2 (10 Gbps), USB-IF Certified, Thunderbolt 3 Compatible, 3 ft. (0.91 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	U428-C03-G2
UPC	037332215031
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.06 lb
WARRANTY	Limited lifetime
COMPLIANCES	RoHS FCC Compliant CE Marked REACH
CERTIFICATIONS	USB-IF

APPLICATION

- Charge and sync a USB-C or Thunderbolt 3 mobile device from a USB-A wall charger up to 3 ft. away
- Connect a printer or scanner to the USB-C port on your computer or laptop
- Transfer data between an external hard drive or flash drive and your computer or laptop
- Connect your computer or laptop to a docking station or hub with a USB-C or Thunderbolt 3 port

RELATIVE HUMIDITY	10% to 85%, Non-Condensing
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
CONNECTOR PLATING	Nickel
CONNECTOR TYPE	USB/Thunderbolt/Lightning
USB SPECIFICATION	USB 3.2 Gen 2 (Up to 10 Gbps)
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	U428-C03-G2 USB Type-C to USB Type-A Cable, M/M, USB-IF Certified, 3 ft.

PRODUCT HIGHLIGHTS

Power Delivery cable provides 3A (60W) power output for charging mobile devices

Supports USB 3.2 Gen 2 speeds up to 10 Gbps to ensure lightning-fast data transfers

Certified by USB-IF to ensure highest-grade construction and performance

Lifetime limited warranty (Worldwide)

Reversible USB-C plug connects in either direction for immediate no-fuss use

USB-C to USB-A cable is

	compatible with all USB-C and Thunderbolt 3 devices
CONTACT PLATING	Gold
SIDEA CONNECTOR1	USB A (MALE)
SIDEB CONNECTOR1	USB C (MALE)
OPERATING TEMPERATURE	14° to 140°F (-10° to 60°C)
OPERATING TEMPERATURE RANGE	14° to 140°F (-10° to 60°C)
STORAGE TEMPERATURE RANGE	-4° to 158°F (-20° to 70°C)
SIDEB CONNECTOR3	USB C (MALE)
TECHNOLOGY	Thunderbolt USB 3.x
CABLE LENGTH	Up to 4ft (up to 1M)
CABLE OUTER DIAMETER (OD)	4.8 mm
CABLE TYPE	Passive
CONNECTOR GROUP	USB-C USB-A
MATERIAL	PVC
CABLE LENGTH RANGE	Up to 4ft (up to 1M)
CONNECTOR	USB C (male) USB A (male)

□□□□:
□□□□:
□□□:
□□: