



Eaton U442-DOCK10-S

USB-C Dock - 4K HDMI, USB 3.2 Gen 1, USB-A Hub Ports, Memory Card, 60W PD Charging

□□□□

PRODUCT NAME	Eaton Tripp Lite series docking station
CATALOG NUMBER	U442-DOCK10-S
UPC	037332213365
PRODUCT LENGTH/DEPTH	1.3 in
PRODUCT HEIGHT	0.51 in
PRODUCT WIDTH	4.5 in
PRODUCT WEIGHT	0.15 lb
WARRANTY	3 year limited
COMPLIANCES	CE Marked RoHS FCC Compliant REACH

APPLICATION

- Play video from your laptop or PC on an HDMI display, such as an HDTV or projector
- Transfer data to and from a USB flash drive or Micro SD memory card
- Charge your notebook or laptop by connecting its wall charger to the USB-C PD Charging port
- Connect a microphone/headset to record a podcast or listen to music

TYPE

Docking Station

CHARGING PORTS DETAILS

- Charge the host laptop with up to 60W (20V/3A) of power via the PD 2.0 charging port
- Two USB-A ports provide up to 0.9A each for connecting mobile devices

NUMBER OF CHARGING PORTS

3

TOTAL CHARGING WATTS

60

DEVICE COMPATIBILITY

Laptop
Chromebook
Computer
Projector
Tablet
Monitor/HDTV

OPERATING HUMIDITY RANGE

10 to 85% RH, Non-condensing

RELATIVE HUMIDITY

5% to 95% RH, Non-Condensing

STORAGE HUMIDITY RANGE

5 to 90% RH, Non-condensing

COLOR

Silver

CABLE JACKET RATING

VW-1

MATERIAL

Aluminum

USB HUB PORTS

Yes

USB POWER DELIVERY (PD) CHARGING SUPPORT	Yes
CABLE JACKET COLOR	White
CHARGING PORTS / AMPS	0.9A 3A
CONNECTOR PLATING	Nickel
PRODUCT FEATURES	EDID Support DSC Support Extended Mode Mirror Mode DisplayPort Alt Mode Bus Powered USB Charging
USB SPECIFICATION	USB 3.0 (up to 5 Gbps) USB 3.1 Gen 1 (up to 5 Gbps) USB 3.2 Gen 1 (up to 5 Gbps)
CABLE JACKET MATERIAL	PVC
COLOR DEPTH	24-bit True color 24-bit True Color
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	Owner's manual U442-DOCK10-S USB-C Dock, Silver
PRODUCT HIGHLIGHTS	Supports Ultra HD 4K resolutions up to 3840 x 2160 @ 30 Hz for crystal-clear video USB-A and memory card ports allow connection of flash drives and other peripherals Plug-and-play operation with no software required for easy, immediate installation Transmits audio/video signals from sources supporting USB DisplayPort Alt Mode Supports 20V 3A (60W) power output for fast-charging compatible mobile devices 3-year limited warranty (Worldwide)
CHARGING PORT TYPE	USB C (FEMALE) USB A (FEMALE)
PACKAGING TYPE	Box
CHROMA SUB SAMPLING	4:4:4

PLUG COLOR	White Blue
HDCP SPECIFICATION	2.2
SIDEA CONNECTOR1	USB C (MALE)
COMPATIBLE DEVICES	Smartphone Chromebook Laptop
SIDEB CONNECTOR1	HDMI (FEMALE)
SIDEB CONNECTOR2	USB A (FEMALE)
DATA PORTS	USB-A - USB 3.2 Gen 1 (5 Gbps) USB A (FEMALE)
SIDEB CONNECTOR3	MICRO SD (FEMALE) HDMI (FEMALE)
SIDEB CONNECTOR4	USB C (FEMALE)
HOST CONNECTOR	USB C (MALE)
CHARGING AMPS PER PORT	0.9 A 3 A
TECHNOLOGY	HDMI USB 3.x
FEATURES	Flex Center
CHARGING PORTS	USB-C: 60W (20V 3A) Power Delivery (PD 2.0)
VIDEO PORTS DETAILS	• HDMI 2.0 • HDCP 2.2
SUPPORTED RESOLUTION	3840x2160 (4K)
NUMBER OF PORTS	5
NUMBER OF USB HUB PORTS	2
POWER CONSUMPTION	2 W
TOTAL NUMBER OF PORTS	5
NUMBER OF MONITORS SUPPORTED	1
CARD SLOTS DETAILS	SD 3.0
RESOLUTIONS SUPPORTED	HDMI: 4K 30Hz (3840 x 2160)
STORAGE TEMPERATURE RANGE	14° to 158°F (-10° to 70°C)
BTUS	6.1 BTU/Hr
MAX SUPPORTED VIDEO RESOLUTION	3840 X 2160 (4K X 2K) @ 30HZ
DATA PORTS DETAILS	USB-A - USB 3.2 Gen 1 (5 Gbps)
CARD SLOTS	MICRO SD (FEMALE)

VIDEO INPUT	USB C (MALE)
VIDEO OUTPUT	HDMI (FEMALE)
VIDEO PORTS	HDMI 2.0 HDMI (FEMALE) HDCP 2.2
USB POWER DELIVERY (PD) CHARGING SPECIFICATION	2
SD CARD SPECIFICATION	Micro SD
