



Eaton U444-06N-HD4K6B

USB-C to HDMI Adapter (M/F) - 4K 60 Hz,
HDCP 2.2, Black

□□□□

PRODUCT NAME	Eaton Tripp Lite series video adapter
CATALOG NUMBER	U444-06N-HD4K6B
UPC	037332203366
PRODUCT LENGTH/DEPTH	1.77 in
PRODUCT HEIGHT	0.59 in
PRODUCT WIDTH	1.16 in
PRODUCT WEIGHT	0.04 lb
WARRANTY	3 year limited
COMPLIANCES	RoHS REACH CE Marked FCC Compliant

□□□□	
AUDIO SPECIFICATION	7.1 Channel Surround Sound
RELATIVE HUMIDITY	20% to 80% RH, Non-Condensing
COLOR	Black
MATERIAL	ABS
CABLE JACKET COLOR	Black
CONNECTOR PLATING	Nickel
CONNECTOR TYPE	Video USB/Thunderbolt/Lightning
PRODUCT FEATURES	3D Video Supported Mirror Mode HDR Support Multi-Resolution Support Bus Powered
USB SPECIFICATION	USB 3.2 Gen 1 (up to 5 Gbps)
CABLE JACKET MATERIAL	PVC
COLOR DEPTH	36-bit Deep color 36-bit Deep Color
PACKAGE CONTENTS	Owner's manual U444-06N-HD4K6B USB 3.2 Gen 1 USB-C to HDMI 4K Adapter (M/F)
PRODUCT HIGHLIGHTS	Plug-and-play operation with no software or drivers required Reversible USB-C plug connects in either direction
	Supports UHD resolutions up to true 4K @ 60 Hz for crystal-clear video 3-year limited warranty (Worldwide) Supports 7.1-channel surround sound Supports USB DisplayPort Alternate Mode for transmitting audio/video
CONTACT PLATING	Gold
PACKAGING TYPE	Box
HDCP SPECIFICATION	2.2
SIDEA CONNECTOR1	USB C (MALE)
SIDEB CONNECTOR1	HDMI (FEMALE)
SIDEB CONNECTOR3	HDMI (FEMALE)
HOST CONNECTOR	USB C (MALE)
TECHNOLOGY	HDMI

□□	
----	--

VIDEO PORTS DETAILS	• HDMI 2.0 • HDCP 1.4 • HDCP 2.2
CONNECTOR GROUP	USB-C HDMI
CONNECTOR	USB C (male) HDMI (female)
SUPPORTED RESOLUTION	1280x720 (720p) 3840x2160 (4K) 1920x1080 (1080p)
NUMBER OF MONITORS SUPPORTED	1
BTUS	2.3 BTU/Hr
MAX SUPPORTED VIDEO RESOLUTION	4096 x 2160 (4K x 2K) @ 60Hz
OPERATING TEMPERATURE RANGE	-4° to 158°F (-20° to 70°C)
STORAGE TEMPERATURE RANGE	-4° to 185°F (-20° to 85°C)
VIDEO INPUT	USB C (MALE)
VIDEO OUTPUT	HDMI (FEMALE)
VIDEO PORTS	HDMI (FEMALE)
NUMBER OF PORTS	1
POWER CONSUMPTION	0.68 W
MAX RESOLUTION	4K/60

□□□□:
□□□□:
□□□:
□□: