




Eaton U444-06N- HD4K6W

USB-C to HDMI Adapter (M/F) - 4K 60 Hz,
HDCP 2.2, White

□□□□

PRODUCT NAME	Eaton Tripp Lite series video adapter
CATALOG NUMBER	U444-06N-HD4K6W
UPC	037332213334
PRODUCT LENGTH/DEPTH	3.9 in
PRODUCT HEIGHT	0.8 in
PRODUCT WIDTH	4.7 in
PRODUCT WEIGHT	0.001 lb
COMPLIANCES	RoHS CE Marked FCC Compliant UKCA

□□□□	
TYPE	Video Adapter
AUDIO SPECIFICATION	7.1 Channel Surround Sound
OPERATING HUMIDITY RANGE	10%-85% RH
STORAGE HUMIDITY RANGE	5%-90% RH
COLOR	White
CABLE JACKET RATING	VW-1
MATERIAL	PVC
CABLE JACKET COLOR	White
CONNECTOR PLATING	Nickel
CONNECTOR TYPE	USB/Thunderbolt/Lightning
	Video
PRODUCT FEATURES	Mirror Mode Bus Powered Multi-Resolution Support 3D Video Supported
USB SPECIFICATION	USB 3.0 (up to 5 Gbps) USB 3.1 Gen 1 (up to 5 Gbps)
CABLE JACKET MATERIAL	PVC
PRODUCT HIGHLIGHTS	Supports UHD resolutions up to 4K @ 60 Hz for crystal-clear video Transmits video signals from sources supporting USB-C DisplayPort Alt Mode Supports USB 3.2 Gen 1 speeds up to 5 Gbps to ensure fast data transfers Reversible USB-C plug connects in either direction for immediate no-fuss use Plug-and-play operation with no software required for easy, immediate installation
CONTACT PLATING	Gold
PACKAGING TYPE	Box
HDCP SPECIFICATION	2.2
SIDEA CONNECTOR1	USB C (MALE)
SIDEB CONNECTOR1	HDMI (FEMALE)
SIDEB CONNECTOR3	HDMI (FEMALE)
HOST CONNECTOR	USB C (MALE)
TECHNOLOGY	HDMI USB 3.x



DATA TRANSFER RATE	5 Gbps
VIDEO PORTS DETAILS	• HDMI 2.0 • HDCP 2.2
CONNECTOR GROUP	USB-C HDMI
CONNECTOR	USB C (male) HDMI (female)
SUPPORTED RESOLUTION	1920x1080 (1080p) 3840x2160 (4K)
MAX SUPPORTED VIDEO RESOLUTION	3840 x 2160 (4K) @ 60Hz
OPERATING TEMPERATURE RANGE	32° to 113°F (0° to 45°C)
STORAGE TEMPERATURE RANGE	14° to 158°F (-10° to 70°C)
VIDEO INPUT	USB C (MALE)
VIDEO OUTPUT	HDMI (FEMALE)
VIDEO PORTS	HDMI (FEMALE)
NUMBER OF PORTS	1
MAX RESOLUTION	4K/60

□□□□:
□□□□:
□□□:
□□: