




Eaton U460-002-2AM-C

USB-C Multiport Adapter, 2x USB-A and 1x USB-C Ports, Card Reader and PD Charging, USB 3.0, White

□□□□

PRODUCT NAME	Eaton Tripp Lite series hub
CATALOG NUMBER	U460-002-2AM-C
UPC	037332193780
PRODUCT LENGTH/DEPTH	1.57 in
PRODUCT HEIGHT	0.43 in
PRODUCT WIDTH	3.7 in
PRODUCT WEIGHT	0.1 lb
WARRANTY	3 year limited
COMPLIANCES	CE Marked REACH FCC Compliant RoHS

Specifications	
TYPE	Multiport Adapter
TOTAL CHARGING WATTS	60
OPERATING HUMIDITY RANGE	10 - 85 % RH, Non-Condensing
RELATIVE HUMIDITY	5% to 90% RH, Non-Condensing
STORAGE HUMIDITY RANGE	5 - 90 % RH, Non-Condensing
COLOR	White
CABLE JACKET RATING	VW-1
MATERIAL	Plastic
USB HUB PORTS	Yes
USB POWER DELIVERY (PD) CHARGING SUPPORT	Yes
CHARGING PORTS / AMPS	1.5A 3A
CONNECTOR PLATING	Nickel
PRODUCT FEATURES	Battery Charging (5V/1.5A Port) Bus Powered UASP Support
USB SPECIFICATION	USB 3.0 (up to 5 Gbps) USB 3.1 Gen 1 (up to 5 Gbps) USB 3.2 Gen 1 (up to 5 Gbps)
CABLE JACKET MATERIAL	PVC
PACKAGE CONTENTS	Owner's manual U460-002-2AM-C USB 3.1 Gen 1 USB-C Portable Hub/Adapter
PRODUCT HIGHLIGHTS	Compact and easy to carry in a pocket, purse or laptop bag Reversible USB-C plug connects in either direction USB-C PD charging port supports power input up to 20V 3A (60W) Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps Plug-and-play operation with no software or drivers required 3-year limited warranty (Worldwide) USB-A port provides up to 5V/1.5A (7.5W) of fast-charging power.



PACKAGING TYPE	Box
PLUG COLOR	Blue White
SIDEA CONNECTOR1	USB C (MALE)
SIDEB CONNECTOR1	USB 3.0 A (FEMALE)
SIDEB CONNECTOR2	USB C (FEMALE)
DATA PORTS	USB-A - USB 3.2 Gen 1 (5 Gbps) USB-C - USB 3.2 Gen 1 (5 Gbps) USB A (FEMALE)
SIDEB CONNECTOR3	MICRO SD (FEMALE) USB 3.0 A (FEMALE)
SIDEB CONNECTOR4	SD (FEMALE)
HOST CONNECTOR	USB C (MALE)
CHARGING AMPS PER PORT	1.5 A 3 A
TECHNOLOGY	USB 3.x
FEATURES	Flex Center
CHARGING PORTS	USB-A: 5V 1.5A (7.5W) USB-C: 60W (20V 3A) Power Delivery (PD 2.0)
DATA TRANSFER RATE	5 Gbps
NUMBER OF PORTS	5
NUMBER OF USB HUB PORTS	2
POWER CONSUMPTION	2 W
NUMBER OF MONITORS SUPPORTED	1
CARD SLOTS DETAILS	SD 3.0 Memory Card slots (SD and MicroSD)
STORAGE TEMPERATURE RANGE	14° to 158°F (-10° to 70°C)
BTUS	6.8 BTU/Hr
DATA PORTS DETAILS	USB-A - USB 3.2 Gen 1 (5 Gbps) USB-C - USB 3.2 Gen 1 (5 Gbps)
CARD SLOTS	SD (FEMALE) MICRO SD (FEMALE)
USB POWER DELIVERY (PD) CHARGING SPECIFICATION	2
SD CARD SPECIFICATION	SD Micro SD



© 2026 〇〇 〇〇〇〇〇〇〇〇