



Eaton U460-003-3AG-C

3-Port USB-C Hub with LAN Port and Power Delivery, USB-C to 3x USB-A Ports and Gbe, USB 3.0, White

□□□□

PRODUCT NAME	Eaton Tripp Lite series hub
CATALOG NUMBER	U460-003-3AG-C
UPC	037332193810
PRODUCT LENGTH/DEPTH	1.575 in
PRODUCT HEIGHT	0.65 in
PRODUCT WIDTH	3.78 in
PRODUCT WEIGHT	0.09 lb
WARRANTY	3 year limited
COMPLIANCES	RoHS REACH CE Marked FCC Compliant



Powering Business Worldwide

APPLICATION

- Save data from your computer to a USB thumb drive or external hard drive
- Access a wired Gigabit Ethernet network in a location with no or spotty Wi-Fi
- Charge your notebook or laptop by connecting its wall charger to the USB-C PD Charging port
- Connect a USB microphone/headset to record a podcast or listen to music
- Write a report using a USB keyboard with your tablet or Android phone

TYPE

Hub

CHARGING PORTS DETAILS

- Charge the host laptop or other PD Charging compatible device with up to 20V 3A (60W) via the PD port
- One dedicated USB-A port provides up to 5V 1.5A (7.5W) of power output to quickly charge mobile devices
- The remaining two USB-A ports each provide 0.9A charging output

NUMBER OF CHARGING PORTS

4

TOTAL CHARGING WATTS

60

DEVICE COMPATIBILITY

Computer
Chromebook
Laptop
Router

OPERATING HUMIDITY RANGE

10 - 85 % RH, Non-Condensing

STORAGE HUMIDITY RANGE

5 - 90 % RH, Non-Condensing

COLOR	White
CABLE JACKET RATING	VW-1
MATERIAL	ABS, PVC
USB HUB PORTS	Yes
USB POWER DELIVERY (PD) CHARGING SUPPORT	Yes
CABLE JACKET COLOR	White
CHARGING PORTS / AMPS	0.9A 1.5A 3A
CONNECTOR PLATING	Nickel
IEEE STANDARDS SUPPORTED	802.3
PRODUCT FEATURES	USB Charging Bus Powered Ethernet Support Remote Wakeup Support UASP Support Auto MDIX Support Battery Charging (5V/1.5A Port) Full Duplex Support Suspend Mode Support
USB SPECIFICATION	USB 3.0 (up to 5 Gbps) USB 3.1 Gen 1 (up to 5 Gbps) USB 3.2 Gen 1 (up to 5 Gbps)
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Straight
NETWORK SPEED	1 Gbps (Gigabit)
PACKAGE CONTENTS	Owner's manual U460-003-3AG-C USB 3.2 Gen 1 Portable Hub/Adapter
PRODUCT HIGHLIGHTS	Plug-and-play operation with no software required for easy, immediate installation Power Delivery port provides 3A (60W) power output for charging connected device Reversible USB-C plug connects in either direction for immediate no-fuss use 3-year limited warranty (Worldwide) Connects you to a wired 10/100/1000 Ethernet network when Wi-Fi is unavailable

	Supports USB 3.2 Gen 1 speeds up to 5 Gbps to ensure fast data transfers
CHARGING PORT TYPE	USB A (FEMALE) USB C (FEMALE)
PACKAGING TYPE	Box
PLUG COLOR	White
POWER SOURCE TYPE	AC Adapter Bus
SIDEA CONNECTOR1	USB C (MALE)
COMPATIBLE DEVICES	Tablet Chromebook Smartphone Laptop
SIDEB CONNECTOR1	USB A (FEMALE)
SIDEB CONNECTOR2	RJ45 (FEMALE)
DATA PORTS	USB C (FEMALE) USB-A - USB 3.2 Gen 1 (5 Gbps) USB A (FEMALE)
SIDEB CONNECTOR3	USB C (FEMALE) USB A (FEMALE)
HOST CONNECTOR	USB C (MALE)
CHARGING AMPS PER PORT	3 A 1.5 A 0.9 A
TECHNOLOGY	Cat5/5e Cat6 USB 3.x
FEATURES	Flex Center
NETWORK COMPATIBILITY	1 Gbps (Gigabit)
CHARGING PORTS	USB-A: 5V 1.5A (7.5W) USB-A: 0.9A USB-C: 60W (20V 3A) Power Delivery (PD 2.0)
DATA TRANSFER RATE	5 Gbps
NUMBER OF PORTS	5
NUMBER OF USB HUB PORTS	4
PORTS	1
POWER CONSUMPTION	3 W
TOTAL NUMBER OF PORTS	5
PORTS DETAIL	Connect to a wired Ethernet network at speeds up to 10/100/1000Mbps (Gigabit)
STORAGE TEMPERATURE RANGE	14° to 158°F (-10° to 70°C)

BTUS	8.5 BTU/Hr
DATA PORTS DETAILS	USB-A - USB 3.2 Gen 1 (5 Gbps)
NETWORK PORTS	RJ45 (FEMALE)
USB POWER DELIVERY (PD) CHARGING SPECIFICATION	20V/3A 60W
