



Eaton USA-19HS

Keyspan USB to Serial Adapter - USB-A Male to DB9 RS232 Male, 3 ft. (0.91 m), TAA


□□□□

PRODUCT NAME	Eaton Tripp Lite series adapter
CATALOG NUMBER	USA-19HS
UPC	672603000413
PRODUCT LENGTH/DEPTH	3.07 in
PRODUCT HEIGHT	0.95 in
PRODUCT WIDTH	1.63 in
PRODUCT WEIGHT	0.077 lb
WARRANTY	3 year limited
COMPLIANCES	FCC Compliant REACH RoHS CE Marked
CERTIFICATIONS	EN 55024 EN 55032



Powering Business Worldwide

□□□□	
DEVICE COMPATIBILITY	Printer
	Router
	Scanner
COLOR	Black
CABLE JACKET COLOR	Black
CONNECTOR PLATING	Nickel
CONNECTOR TYPE	Serial/parallel USB/Thunderbolt/Lightning
PRODUCT FEATURES	Bus Powered Driver Required TAA Compliant
USB SPECIFICATION	USB 2.0 (up to 480 Mbps)
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	Owner's Manual USB-A cable, 3 ft. (0.91 m) USA-19HS Keyspan High-Speed RS232 to USB Adapter
PRODUCT HIGHLIGHTS	Plug-and-play operation with no software required for easy, immediate installation 3-year limited warranty (Worldwide) Supports data transfer speeds up to 230 Kbps to ensure reliable data transfers Works with 32- and 64-bit Windows and macOS X (see model support page) Detachable 3 ft. USB cable included
CONTACT PLATING	Gold
SIDEA CONNECTOR1	USB A (MALE)
SIDEB CONNECTOR1	DB9 (MALE)
SIDEB CONNECTOR3	DB9 (MALE)
HOST CONNECTOR	USB A (MALE)
TECHNOLOGY	USB
CABLE LENGTH	3 Foot
NUMBER OF PORTS	2
TOTAL NUMBER OF PORTS	2
CABLE COMPATIBILITY	DB9 (Female)
CABLE OUTER DIAMETER (OD)	3.8mm
CONNECTOR GROUP	DB9



	USB-A
TAA COMPLIANCE	Yes
WIRE GAUGE (AWG)	28
CABLE LENGTH RANGE	Up to 4ft (up to 1M)
CONNECTOR	USB A (male) DB9 (male)
