



□□□□

## Eaton 121606

Eaton Moeller® series C22 Changeover switch, With thumb-grip, momentary, 2 N/O, Screw connection, 3 positions, Bezel: black

□□□□

<b>PRODUCT NAME</b>	Eaton Moeller® series C22 Changeover switch
<b>CATALOG NUMBER</b>	121606
<b>PRODUCT LENGTH/DEPTH</b>	73 mm
<b>PRODUCT HEIGHT</b>	30 mm
<b>PRODUCT WIDTH</b>	30 mm
<b>PRODUCT WEIGHT</b>	0.023 kg
<b>CERTIFICATIONS</b>	CSA File No.: 165628 UL 508 UL Listed CSA-C22.2 No. 14-05 and 94-M91 CE marking CSA Class No.: 321103 IEC/EN 60947-5-1 UL Category Control No.: NKCR UL File No.: E29184 CSA certified VDE 0660



Powering Business Worldwide

□□□□

<b>TYPE</b>	Selector switch actuator
<b>ACTUATOR COLOR</b>	Black
<b>PRODUCT CATEGORY</b>	RMQ Compact
<b>ACTUATOR FUNCTION</b>	Spring-return Momentary
<b>ELECTRIC CONNECTION TYPE</b>	Screw connection
<b>FITTED WITH:</b>	Front ring
<b>OPERATING FREQUENCY</b>	2000 Operations/h
<b>POLLUTION DEGREE</b>	3
<b>CLIMATIC PROOFING</b>	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
<b>CONNECTION TO SMARTWIRE-DT</b>	No
<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>	4000 V AC
<b>ACTUATOR TYPE</b>	Toggle
<b>NUMBER OF CONTACTS (CHANGE-OVER CONTACTS)</b>	0
<b>NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)</b>	0
<b>NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)</b>	2
<b>OPENING DIAMETER</b>	22.5 mm
<b>OPERATING TORQUE</b>	0.3 Nm
<b>RATED INSULATION VOLTAGE (UI)</b>	250 V
<b>BEZEL COLOR</b>	Black
<b>BEZEL MATERIAL</b>	Plastic
<b>DESIGN</b>	With thumb-grip
<b>MOUNTING POSITION</b>	As required
<b>RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)</b>	1 kA
<b>CONNECTION TYPE</b>	Screw connection
<b>OVERVOLTAGE CATEGORY</b>	III
<b>DEGREE OF PROTECTION</b>	NEMA 3R IP65
<b>LIFESPAN, MECHANICAL</b>	1,000,000 Operations

□□

<b>DECLARATIONS OF CONFORMITY</b>	<a href="#">eaton-pushbutton-declaration-of-conformity-uk250928en.pdf</a>
<b>MCAD MODEL</b>	<a href="#">eaton-switches-mcad-drawings-wahltaste-normal.dwg</a>
□□□□□	<a href="#">eaton-rmq-titan-c22-pv-compact-program-emergency-buttons-instruction-leaflet-il04716025z.pdf</a>
□□□	<a href="#">eaton-operating-pushbutton-wiring-diagram-004.eps</a>
□□□□□	<a href="#">eaton-operating-diagram-contact-travel-diagram.eps</a>
□□	<a href="#">eaton-operating-switch-changeover-switch-dimensions-002.eps</a>  <a href="#">eaton-operating-changeover-switch-3d-drawing.eps</a>

