



□□□□

Eaton 121607

Eaton Moeller® series C22 Changeover switch, With thumb-grip, maintained, 2 NC, Screw connection, 3 positions, Bezel: black

□□□□

PRODUCT NAME	Eaton Moeller® series C22 Changeover switch
CATALOG NUMBER	121607
PRODUCT LENGTH/DEPTH	73 mm
PRODUCT HEIGHT	30 mm
PRODUCT WIDTH	30 mm
PRODUCT WEIGHT	0.023 kg
CERTIFICATIONS	IEC/EN 60947-5-1 CSA File No.: 165628 UL File No.: E29184 CE marking UL 508 CSA-C22.2 No. 14-05 and 94-M91 UL Listed VDE 0660 CSA Class No.: 321103 UL Category Control No.: NKCR CSA certified
CATALOG NOTES	Contacts with safety function, by positive opening to IEC/EN 60947-5-1



Powering Business Worldwide

□□□□

TYPE	Selector switch actuator
ACTUATOR COLOR	Black
PRODUCT CATEGORY	RMQ Compact
FEATURES	Positive opening
ACTUATOR FUNCTION	Switching function latching Maintained
ELECTRIC CONNECTION TYPE	Screw connection
FITTED WITH:	Front ring
OPERATING FREQUENCY	2000 Operations/h
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
CONNECTION TO SMARTWIRE-DT	No
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4000 V AC
ACTUATOR TYPE	Toggle
ACTUATOR TRAVEL AND ACTUATION FORCE (DIN EN 60947-5-1)	4.65 mm
FORCE FOR POSITIVE OPENING - MIN	30 N
KNOB TRAVEL	5.7 mm
NUMBER OF CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	2
NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	0
OPENING DIAMETER	22.5 mm
OPERATING TORQUE	0.3 Nm
RATED INSULATION VOLTAGE (UI)	250 V
BEZEL COLOR	Black
BEZEL MATERIAL	Plastic
DESIGN	With thumb-grip
MOUNTING POSITION	As required
RATED CONDITIONAL SHORT-CIRCUIT CURRENT	1 kA

□□

DECLARATIONS OF CONFORMITY	eaton-pushbutton-declaration-of-conformity-uk250928en.pdf
MCAD MODEL	eaton-switches-mcad-drawings-wahlteste-normal.dwg
□□□□□	eaton-rmq-titan-c22-pv-compact-program-emergency-buttons-instruction-leaflet-il04716025z.pdf
□□□	eaton-operating-pushbutton-wiring-diagram-005.eps
□□□□□	eaton-operating-adapter-key-operated-actuator-contact-travel-diagram.eps
□□	eaton-operating-switch-changeover-switch-dimensions-002.eps eaton-operating-changeover-switch-3d-drawing.eps

