



Eaton 178856

Eaton xComfort KLV LV systems Final Distribution Boards. Hollow wall expansion kit with plug-in terminal 3 row, form of delivery for projects, F3HWP-4PR

□□□□

PRODUCT NAME	Eaton xComfort KLV project delivery form
CATALOG NUMBER	178856
PRODUCT LENGTH/DEPTH	40 mm
PRODUCT HEIGHT	590 mm
PRODUCT WIDTH	360 mm
PRODUCT WEIGHT	2.7 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	IEC/EN 62208, IEC/EN 60670-24 (PD)



Powering Business Worldwide

USED WITH	Installation distribution boards Basic device KLV for projects
------------------	--

SPECIAL FEATURES	<ul style="list-style-type: none"> • IP30 • Protection Class II • Sheet steel door, white (RAL 9016)
-------------------------	---

TYPE	<ul style="list-style-type: none"> • Basic device • Installation distribution boards • KLV for projects
-------------	--

ACCESSORY/SPARE PART TYPE	Other Accessory
----------------------------------	--------------------

FITTED WITH:	Imprintable sheet 3D adjustment element for mounting Cable retainer Neutral-/protective conductor terminal Installation instructions Front cover Device support rails
---------------------	---

FREQUENCY RATING	50 Hz
-------------------------	-------

COLOR	Traffic white (RAL 9016)
--------------	--------------------------

DEGREE OF PROTECTION	IP30 IK05 (impact resistance)
-----------------------------	----------------------------------

TERMINAL TYPE	Plug-in terminals
----------------------	-------------------

AMBIENT OPERATING TEMPERATURE DETAILS	-5 °C - 40 °C
--	---------------

APPLICATION	Indoor (installation site)
--------------------	----------------------------

COVER/DOOR COLOR	White
-------------------------	-------

MATERIAL	Sheet steel, powder-coated Polystyren (plastic)
-----------------	--

NUMBER OF ROWS	3
-----------------------	---

INSTALLATION TYPE	Hollow-wall mounting
--------------------------	----------------------

MOUNTING METHOD	Hollow wall
------------------------	-------------

FUNCTIONS	Basic device Additional equipment
------------------	--------------------------------------

MODULE RACK TYPE	Rail frame
-------------------------	------------

NUMBER OF MODULE SPACE UNITS PER ROW	12
---	----

PROTECTION CLASS	II (totally insulated)
-------------------------	------------------------

PROTECTIVE SHROUDING MATERIAL	Plastic
--------------------------------------	---------

[eaton-xcomfort-compact-distribution-boxes-brochure-br014015en-en-us.pdf](#)

