



## Eaton 186054

Eaton C30 Pushbutton, flat, momentary, 2 N/O, Cable (black) with non-terminated end, 4 pole, 1 m, Bezel: chrome

□□□□

<b>PRODUCT NAME</b>	Eaton Moeller® series C30 Pushbutton
<b>CATALOG NUMBER</b>	186054
<b>PRODUCT LENGTH/DEPTH</b>	1060 mm
<b>PRODUCT HEIGHT</b>	46 mm
<b>PRODUCT WIDTH</b>	36 mm
<b>PRODUCT WEIGHT</b>	0.065 kg
<b>CERTIFICATIONS</b>	IEC/EN 60947-5-1 VDE 0660 CSA Class No.: 321103 CSA File No.: 165628 UL 508 CSA-C22.2 No. 14-18 and No. 94.2-15 CE marking UL Category Control No.: NKCR UL File No.: E29184 UL CSA



Powering Business Worldwide

□□□□

<b>TYPE</b>	Pushbutton actuator
<b>ACTUATOR COLOR</b>	Without button plate
<b>ACTUATOR FUNCTION</b>	Momentary Spring-return
<b>ELECTRIC CONNECTION TYPE</b>	Cable
<b>FITTED WITH:</b>	Front ring
<b>OPERATING FREQUENCY</b>	3600 Operations/h
<b>POLLUTION DEGREE</b>	3
<b>CLIMATIC PROOFING</b>	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
<b>CONNECTION TO SMARTWIRE-DT</b>	No
<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>	800 V AC
<b>BEZEL COLOR</b>	Chrome
<b>CABLE MATERIAL</b>	PUR
<b>ACTUATING FORCE</b>	5 N
<b>ACTUATOR DIAMETER</b>	29.7 mm
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	70 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>NUMBER OF COMMAND POSITIONS</b>	1
<b>NUMBER OF CONTACTS (CHANGE-OVER CONTACTS)</b>	0
<b>NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)</b>	0
<b>NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)</b>	2
<b>BEZEL MATERIAL</b>	Metal
<b>DESIGN</b>	Flat Cable end open
<b>MOUNTING POSITION</b>	As required
<b>RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)</b>	1 kA
<b>CONNECTION TYPE</b>	Cable (black) with non-terminated end, 4 pole
<b>CABLE LENGTH</b>	1 m

□□

<b>DECLARATIONS OF CONFORMITY</b>	<a href="#">eaton-pushbutton-declaration-of-conformity-uk250928en.pdf</a>
□□□□□	<a href="#">IL047021ZU</a>
□□□	<a href="#">eaton-operating-c22-pushbutton-wiring-diagram-003.eps</a>
□□□□□	<a href="#">eaton-operating-diagram-contact-travel-diagram.eps</a>
□□	<a href="#">eaton-operating-c30-pushbutton-dimensions-003.eps</a> <a href="#">eaton-operating-c30-pushbutton-3d-drawing.eps</a>

