



□□□□□

Eaton 188122

Eaton Moeller® series M30 Potentiometer, flat front, M30, 30.5 mm, Without scale/inscription, R 47 kΩ, P 0.5 W, Front ring stainless steel

□□□□

PRODUCT NAME	Eaton Moeller® series M30 Potentiometer
CATALOG NUMBER	188122
PRODUCT LENGTH/DEPTH	36 mm
PRODUCT HEIGHT	63 mm
PRODUCT WIDTH	46 mm
PRODUCT WEIGHT	0.055 kg
CERTIFICATIONS	IEC/EN 60947 VDE 0660
CATALOG NOTES	Without scale/inscription



Powering Business Worldwide

□□□□

TYPE	Potentiometer
ELECTRIC CONNECTION TYPE	Screw connection
FITTED WITH:	3 individual screw terminals
POLLUTION DEGREE	3
ACCURACY	± 10 % (linear), Resistance value
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
CONNECTION TO SMARTWIRE-DT	No
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4000 V AC
BEZEL COLOR	Stainless steel
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
NUMBER OF REVOLUTIONS - MAX	1
NUMBER OF REVOLUTIONS - MIN	1
OPENING DIAMETER	30 mm
RATED INSULATION VOLTAGE (UI)	250 V
RATED POWER	0.5 VA
DESIGN	Flat front
MOUNTING POSITION	As required
OVERVOLTAGE CATEGORY	III
DEGREE OF PROTECTION	IP66 NEMA Other
POWER CONSUMPTION	0.5 W
LIFESPAN, MECHANICAL	25,000 Operations
SHOCK RESISTANCE	Not planned
RESISTANCE	47000 Ohm
TERMINAL CAPACITY (SOLID)	0.5 - 1.5 mm ²
TERMINAL CAPACITY (STRANDED)	0.5 - 1.5 mm ²
TIGHTENING TORQUE	0.5 Nm, Screw terminals

□□

DECLARATIONS OF CONFORMITY

[eaton-key-operated-actuator-declaration-of-conformity-uk251346en.pdf](#)

[eaton-key-operated-actuator-declaration-of-conformity-uk251347en.pdf](#)

□□□□□

[eaton-operating-devices-m30-rmq-titan-flat-front-instruction-leaflet-il047019zu.pdf](#)

[IL047030ZU](#)

□□□

[eaton-operating-potentiometer-m30-wiring-diagram.eps](#)

□□

[eaton-operating-m30-dimensions-006.eps](#)

[eaton-operating-m30-dimensions-004.eps](#)

[eaton-operating-m30-potentiometer-dimensions.eps](#)

[eaton-operating-m30-dimensions-005.eps](#)

[eaton-operating-m30-potentiometer-3d-drawing.eps](#)

□□/□□

[RMQ small E-Stop emergency-stop button](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

