

## Eaton 199559

Eaton Moeller® series DILH Auxiliary contact module, 2 pole, Ith= 10 A, 1 N/O, 1 NC, Side mounted, Screw terminals, DILH600 - DILH800

<b>PRODUCT NAME</b>	Eaton Moeller® series DILH auxiliary contact module
<b>CATALOG NUMBER</b>	199559
<b>PRODUCT LENGTH/DEPTH</b>	77 mm
<b>PRODUCT HEIGHT</b>	77 mm
<b>PRODUCT WIDTH</b>	15 mm
<b>PRODUCT WEIGHT</b>	0.056 kg
<b>CERTIFICATIONS</b>	CSA Class No.: 3211-04 CSA file No. 012528 IEC/EN 60947-4-1 UL 508 CSA-C22.2 No. 14-05 CE marking IEC/EN 60947 VDE 0660 UL CSA UL Category Control No.: NKCR UL File No.: E29184 UL Listed CSA certified

<b>ELECTRIC CONNECTION TYPE</b>	Screw connection
---------------------------------	------------------

<b>AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MAX</b>	40 °C
-------------------------------------------------------	-------

<b>AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MIN</b>	-25 °C
-------------------------------------------------------	--------

<b>AMBIENT STORAGE TEMPERATURE - MAX</b>	80 °C
------------------------------------------	-------

<b>AMBIENT STORAGE TEMPERATURE - MIN</b>	-40 °C
------------------------------------------	--------

<b>NUMBER OF CONTACTS (CHANGE-OVER CONTACTS)</b>	0
--------------------------------------------------	---

<b>NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)</b>	1
------------------------------------------------------	---

<b>NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)</b>	1
----------------------------------------------------	---

<b>NUMBER OF SWITCHES (FAULT SIGNAL)</b>	0
------------------------------------------	---

<b>MOUNTING METHOD</b>	Side mounting
------------------------	---------------

<b>MODEL</b>	Top mounting
--------------	--------------

<b>LAMP HOLDER</b>	None
--------------------	------

<b>RATED OPERATIONAL CURRENT (IE) AT AC-15, 220 V, 230 V, 240 V</b>	6 A
---------------------------------------------------------------------	-----

<b>DECLARATIONS OF CONFORMITY</b>
-----------------------------------

<a href="#">eaton-accessory-declaration-of-conformity-uk251303en.pdf</a>
--------------------------------------------------------------------------

<a href="#">IL034095ZU</a>
----------------------------

<b>PROJECT NAME:</b>
----------------------

<b>PROJECT NUMBER:</b>
------------------------

<b>PREPARED BY:</b>
---------------------

:
---



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

